



Included:

- 1 x PRM-5-EUR
- 3 x probes
- 1 x crocodile clip
- 1 x carrying case
- 1 x user manual

Accessories

1324 Unidreh accessory set allows a perfect and easy connection to CEE 16 A and CEE 32 A sockets, safety cert.: CAT II, 1000 V

PRM-5-EUR
Phase Rotation Tester

Functions

- Phase sequence display with LEDs
- Display of a missing or incorrectly connected outer conductor

Product information

- Fast detection of phase sequence in three-phase supply
- Voltage range from 100 to 700 V, Frequency range 16 to 400 Hz

Product highlights

- No battery needed
- Robust housing with rubber protective cover
- Securely connected test leads
- Measurement category CAT IV, 600 V

Technical specifications

Display	LED for anticlockwise, clockwise, faulty connection
Voltage range	100 ... 700 V
Frequency range	16 ... 400 Hz
Test current	≤3,5 mA
Safety cert	DIN VDE 0411/EN 61010-1/ DIN VDE 0413-7, EN 61557-7
Measurement category	CAT IV / 600 V
Power supply	from test object
Dimensions	137 x 65 x 33 mm
Weight	approx. 253 g

Accessories:



Unidreh accessory set
Model 1324



Carrying case
Model 1150



Crocodile clips for conductor rails
Model 391511 (red)
Model 391512 (black)

Ordering Information:

Description	Model	Article no.
PRM-5-EUR	PRM-5-EUR	4375961
UNIdreh accessory set	1324	2146183
Carrying case	1150	2145755
Crocodile clip for conductor rail		
Red	391511	2146861
Black	391512	2146877



Included:

- 1 x PRM-6-EUR
- 2 x batteries 1.5 V, IEC LR 03
- 3 x test leads
- 3 x probes
- 3 x crocodile clips
- 1 x carrying case
- 1 x user manual

PRM-6-EUR
Motor and Phase Rotation Tester

Functions

- Phase sequence display with LCD
- Display of a missing or incorrectly connected outer conductor
- Non-contact motor rotation indicator when the motor is running
- De-energised identification of motor connections (U, V, W) via a manual drive

Product information

- Fast detection of phase sequence in three-phase supply
- Voltage range from 40 to 700 V, Frequency range 16 to 400 Hz

Product highlights

- Robust housing with rubber protective cover
- Detachable test leads
- Measurement category CAT IV, 600 V
- Back light
- Testing rotary field direction possible without batteries, or with empty batteries

Technical specifications

Display	LCD
Phase sequence indication	40...700 V / 16...60 Hz 50...700 V / 60...400 Hz
Non-Contact Motor rotation indicator	16...400 Hz
Detection of motor connections	>0,65 V / 2....100 Hz
Test current	≤3,5 mA
Safety cert	DIN VDE 0411/EN 61010-1/ DIN VDE 0413-7, EN 61557-7
Measurement category	CAT IV / 600 V
Power supply	2x batteries 1.5 V, IEC LR 03 (AAA), Micro
Dimensions	137 x 65 x 33 mm
Weight	approx. 170 g

Accessories:



Unidreh accessory set
Model 1324



Carrying case
Model 1150



Crocodile clips for conductor rails
Model 391511 (red)
Model 391512 (black)



TL-PRM-6 test lead set for PRM-6-EUR
Model TL-PRM-6

Ordering Information:

Description	Model	Article no.
PRM-6-EUR	PRM-6-EUR	4633222
UNIdreh accessory set	1324	2146183
Carrying case	1150	2145755
Crocodile clip for conductor rail		
Red	391511	2146861
Black	391512	2146877
TL-PRM-6 test lead set for PRM-6-EUR		
(Spare part)	TL-PRM-6	4692870