


TM55 Pocket Fold-Up Food Thermometer




- Applications:**
- Food Industry
 - Frozen and semi-solid samples
 - Liquid solutions
 - Agriculture (soil)
 - Laboratories

Splash-proof (IP65) with folding 2.4" stainless steel probe is NSF certified for measuring liquids, pastes, and semi-solid food.

Features

- Measures from -40 to 482°F (-40 to 250°C) with 2.4" (61mm) stainless steel probe (NSF certified)
- Fast response time at < 5 seconds in moving liquid
- Large LCD display with 0.1° resolution
- Basic accuracy: ±1°F/0.5°C
- Auto power off (with disable) after 1 hour or when probe is placed in stored position
- Probe can be positioned from 0° (storage) to 180° angle
- Ultrasonically welded housing (waterproof IP65 rated) with anti-microbial additive
- Built-in magnetized strip attaches to refrigerator
- Dishwasher safe (top rack)
- Dimensions: 4.6x1.5x0.8" (116 x 38 x 20mm); Weight: 1.5oz (41.2g)
- Complete with CR2032 battery



Adjustable folding probe from 0° to 180° angle

Ordering

TM55..... Pocket Fold-up Food Thermometer

