



### Point of sale display for TREDUX

#### TREDUX-Display

With TREDUX HellermannTyton has set a new standard in heat shrink tubing. TREDUX offers a complete range of thin, medium and thick wall tubing cut into 1 meter length. All tubing are labeled with an EAN barcode securely packed in display boxes. They can be removed individually for occasional use in smaller quantities. With the practical, valuable metal point of sale display is an optimal product presentation guaranteed. The following table is a proposed content for a TREDUX-Display.

#### Features and benefits

- Complete range of thin, medium- and thick wall heatshrink tubing in one display
- All tubings can be sold in single 1 meter length or entire carton
- Pick of single tube possible allowing job specific purchasing
- Optimised stock based on usage based display content
- Holder for end user brochures available attached to display



The TREDUX-Display.



TYPE	Content	Supplied Ø D min.	Recov. Ø d max.	Wall (WT)	Pack Cont.	Colour	Tools	Article-No.
<b>TREDUX-Display</b>								
TREDUX-Display	-	-	-	-	1 pc.	Blue (BU)	30	319-30000
<b>TREDUX - thin wall</b>								
TREDUX-1.5/0.5	1	1.5	0.5	0.45	20 pcs.	Black (BK)	30	319-00150
TREDUX-3/1	1	3.0	1.0	0.55	20 pcs.	Green-Yellow (GNYE)	30	319-00307
TREDUX-6/2	1	6.0	2.0	0.65	15 pcs.	Green-Yellow (GNYE)	30	319-00607
TREDUX-12/4	1	12.0	4.0	0.80	10 pcs.	Green-Yellow (GNYE)	30	319-01207
TREDUX-24/8	1	24.0	8.0	1.20	5 pcs.	Black (BK)	30	319-02400
TREDUX-3/1	2	3.0	1.0	0.55	20 pcs.	Black (BK)	30	319-00300
TREDUX-6/2	2	6.0	2.0	0.65	15 pcs.	Black (BK)	30	319-00600
TREDUX-12/4	4	12.0	4.0	0.80	10 pcs.	Black (BK)	30	319-01200
<b>TREDUX MA47 medium wall - with adhesive liner</b>								
TREDUX-MA47-19/6	1	19.0	6.0	2.40	10 pcs.	Black (BK)	30;32	323-50190
TREDUX-MA47-40/12	1	40.0	12.0	2.50	4 pcs.	Black (BK)	30;32	323-50400
TREDUX-MA47-30/8	2	30.0	8.0	2.60	6 pcs.	Black (BK)	30;32	323-50300
<b>TREDUX HA47 thick wall - with adhesive liner</b>								
TREDUX-HA47-19/6	1	19.0	6.0	2.70	10 pcs.	Black (BK)	32	321-50190
TREDUX-HA47-33/8	1	33.0	8.0	3.20	5 pcs.	Black (BK)	32	321-50330
TREDUX-HA47-45/12	1	45.0	12.0	4.10	4 pcs.	Black (BK)	32	321-50450

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content.

Recommended Tools		
	30	32
	H6100	CHG900
	566	565

For more information on toolings please refer to the Application Tooling chapter.



Add items to your watchlist!

[www.HT.click/49-228](http://www.HT.click/49-228)

