

PRODUCT-DETAILS

TS1025HF

CABLE TIE 20LB NAT NYL 4IN FLM RET



General Information

Extended Product Type	TS1025HF
Product ID	7TCG054360R0062
EAN	5414363059912
Catalog Description	CABLE TIE 20LB NAT NYL 4IN FLM RET
Long Description	Flame Retardant Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length 100mm (3.94 Inches), Width 2.5mm (0.098 Inches), Tensile Strength Rating of 90 Newtons (20 Pounds)

Ordering

EAN	5414363059912
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.001 lb .454 g
--------------------	-------------------

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	10000 piece

Additional Information

Brand / Label	Catamount
Bundle Diameter	0.94 in 24 mm
Color	Natural
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	FLAME RETARDANT 100 X 2.5
Product Type	Flame Retardant
Tensile Strength	20 lb 90 N
UPC	786210499345

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TS1025HF
Instructions and Manuals	TS1025HF

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

