

PRODUCT-DETAILS

# TS1435HF

## CABLE TIE 40LB NAT NYL 5.5IN FLM RT



### General Information

Extended Product Type	TS1435HF
Product ID	7TCG054360R0063
EAN	5414363059929
Catalog Description	CABLE TIE 40LB NAT NYL 5.5IN FLM RT
Long Description	Flame Retardant Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length 140mm (5.51 Inches), Width 3.5mm (0.138 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds)

### Ordering

EAN	5414363059929
Customs Tariff Number	3926909990

### Dimensions

Product Net Weight	.002 lb .907 g
--------------------	-------------------

### Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	10000 piece

---

### Additional Information

Brand / Label	Catamount
Bundle Diameter	1.42 in 36 mm
Color	Natural
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	Flame Retardant
Tensile Strength	40 lb 180 N
UPC	786210567778

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TS1435HF
Instructions and Manuals	TS1435HF

---

### Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

---

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

