

PRODUCT-DETAILS

TS2045HF

CABLE TIE 50LB NAT NYL 8IN FLM RET



General Information

Extended Product Type	TS2045HF
Product ID	7TCG054360R0064
EAN	5414363059936
Catalog Description	CABLE TIE 50LB NAT NYL 8IN FLM RET
Long Description	Flame Retardant Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length 200mm (7.87 Inches), Width 4.5mm (0.177 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds)

Ordering

EAN	5414363059936
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.003 lb 1.361 g
--------------------	--------------------

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	10000 piece

Additional Information		
Brand / Label	Catamount	
Bundle Diameter	2 in 50.8 mm	
Color	Natural	
Lock Type	Plastic Pawl	
Material	Nylon/Polyamide 6.6	
Number of Batteries	0	
Product Name	CATAMOUNT FASTENING PRODUCTS	
Product Type	Flame Retardant	
Tensile Strength	50 lb 222 N	
UPC	786210598222	

Certificates and Declarations (Document Number)		
Data Sheet, Technical Information	TS2045HF	
Instructions and Manuals	TS2045HF	

Classifications		
ETIM 6	EC000046 - Cable tie	
ETIM 7	EC000046 - Cable tie	
UNSPSC	39121703	
WEEE Category	Product Not in WEEE Scope	
IDEA Granular Category Code (IGCC)	5034 >> Cable ties	

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

