

MILAN S.r.l. a socio unico

Head Office – Export department:

Viale Europa, 74
20090 Cusago (MI) Italy
T. +39 02 9039.4556-4158
F. +39 02 9039.4551
www.taskercables.com

Ufficio Commerciale e Centro Distribuzione

Viale Europa 72 Strada F12
20090 Cusago (MI) Italy
T. +39 02 9039.0037-0059
F. +39 02 9039.0049
www.tasker.it

Technical Datasheet



tasker® TSK52 – 2x0,75 mm² - Flat Audio Divisible Cable



CATEGORY Flat Cable (See Audio Catalogue)

- A:** Red and Black Soft PVC Sheath.
Outer cable dimension 2,50x5,00 mm (±0,10) mm.
- B:** Both conductors in CCA - Formation with 0,20 mm wires.
Nominal cross section 2x0,75 mm².

CUSTOM This product is also available in L.S.Z.H., PE, PUR.

Cable Properties

Conductor Resistance	32 Ω/Km ± 5%
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C / 16.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		