





12-Meter USB 2.0 Extension Cable TU2-EX12(V1.0R)

The 12-Meter USB 2.0 Extension Cable, model TU2-EX12, is perfect for extending the distance between USB devices and your computer. Features one male and one female Type A USB 2.0 port. Transfer data at high speeds up to 480Mbps with maximum reliability and performance.


FEATURES

- Compliant with USB 2.0, 1.1, and 1.0 (Type A ports)
- 12 meter (39 ft.) USB 2.0 extension cable
- One male and one female Type A USB 2.0 port
- Supported USB speeds: High-Speed (480Mbps), Full-Speed (12Mbps),and Low-Speed (1.5Mbps)
- Repeats the USB signal to maximum consistency and performance at distance up to 36 m (118 ft.)
- Upstream: supports High-Speed and Full-Speed
- Downstream: supports High-Speed, Full-Speed, and Low-Speed
- 2-year limited warranty

SPECIFICATIONS

HARDWARE	
Interface	• USB 2.0, 1.1, 1.0 compliant (Type A)
Data Rate	High-Speed: 480Mbps Full-Speed: 12Mbps Low-Speed: 1.5Mbps
Connector	USB Type A Male to Female
Cable Length	• 12 meters (39 feet)
Max Distance	• 36 meters (118 feet)
Weight	• 430 g (15.2 oz.)
Operating Temperature	• Operating: 0° ~ 40° C (32° ~ 104° F) • Storage: -20° ~ 85° C (-4° ~ 185° F)
Humidity	Max. 90% (non-condensing)
Certifications	• CE, FCC

NETWORKING SOLUTIONS



PACKAGE CONTENTS

TU2-EX12

Multi-Language Quick Installation Guide

RELATED PRODUCTS

TU2-400E	4-Port USB Hub

CONTACT INFORMATION

TRENDNET

20675 Manhattan Place,Torrance, CA 90501 USA Tel: 1-310-961-5500 Fax: 1-310-961-5511 Web: www.trendnet.com Email: sales@trendnet.com **1-888-326-6061**