



TY 100-18X-C

E1518229

BUNTBAND, TY-FAST, 100x2.5mm, SVART, PLASTTUNGA



Product Properties:

Band closure	Plastic lip/-cam
Material quality	Polyamide (PA)
Model	Internal tooting
Operating temperature	-40-115 °C
Solvable fastener	No
Text strip	None
Transparent	No
Type of fastening	None
UV-stable acc. ASTM D6779	Yes
Colour	Black
Surface protection	Untreated
Material	Plastic
Halogen free	Yes
Inflammability class of insulation material according to with UL94	V2
Max. tensile force	80 N

Dimensions:

MOQ	100 .
Unit	pcs

Length belt/tape/tie	100 mm
Tie thickness	1 mm
Band width	2.5 mm
Max. tensile force	80 N

Approvals:

Approved according to Lloyd's Register TA	Yes
MIL approval	Yes
Inflammability class of insulation material according to with UL94	V2
UL approval	Yes

Compliance:

Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (233 Subs. 17 Jan 2023)
RoHS	RoHS 3 (2015/863)
US TSCA	No (5 PBT Subs, Feb 2021)

Other information:

ETIM-Class	EC000046 - Cable tie
ETIM-Release	7.0
Trademark	Thomas & Betts
Product Group	Cable ties, TY-FAST
Search Description	TY 100-18X-100, 7TCG054360R0430, TY100-18X-C
Alternative SKU	TY100-18X-C

Logistic information:

Barcode	541502252432
Country of origin	CN
E-no	E1518229
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	100 .
Stock code	TY 100-18X-C
Taric code	39269097
Unit	pcs