

UNIVERSAL ENCLOSURES

Flanged Comms Boxes

Flanged Low profile and deep profile plastic housings with removable end panels. Designed for Surface Mounted communication equipment such as Wi-Fi routers.

- Stylishly designed ABS plastic case with double detachable panels
- Flanged sides for surface or wall mounting
- Flame resistant ABS (UL94-V0), 24 sizes, available in off-white
- Equipped with built-in bosses for PCB mounting
- Suitable for WiFi access points, measuring equipment, controller communication applications

SPECIFICATION

Materials	ABS UL94-V0
Protection class	IP40
Operating temperature	-10°C to +60°C
Standard colours	Off-white
Standard unit includes	Top Cover, Flanged Base, x2 Panels, x4 Self Tapping Screws

TAKACHI	LENGTH	WIDTH	HEIGHT
PFF10-2-7W	67.3mm	124.3mm	22.5mm
PFF10-2-10W	100.3mm	124.3mm	22.5mm
PFF10-4-7W	67.3mm	124.3mm	35mm
PFF10-4-10W	100.3mm	124.3mm	35mm
PFF13-3-9W	85.3mm	149.3mm	25mm
PFF13-3-13W	125.3mm	155.3mm	25mm
PFF13-4-9W	85.3mm	149.3mm	40mm
PFF13-4-13W	125.3mm	155.3mm	40mm
PFF15-3-10W	100.4mm	180.4mm	30mm
PFF15-3-15W	150.4mm	180.4mm	30mm
PFF15-5-10W	100.4mm	180.4mm	45mm
PFF15-5-15W	150.4mm	180.4mm	45mm
PFF18-4-12W	120.4mm	205.4mm	35mm
PFF18-4-18W	175.4mm	205.4mm	35mm
PFF18-5-12W	120.4mm	205.4mm	50mm
PFF18-5-18W	175.4mm	205.4mm	50mm
PFF20-4-13W	135.5mm	230.5mm	40mm
PFF20-4-20W	200.5mm	230.5mm	40mm
PFF20-6-13W	135.5mm	230.5mm	60mm
PFF20-6-20W	200.5mm	230.5mm	60mm
PFF24-4-17W	165.5mm	270.5mm	42.5mm
PFF24-4-24W	240.5mm	270.5mm	42.5mm
PFF24-6-17W	165.5mm	270.5mm	60mm
PFF24-6-24W	240.5mm	270.5mm	60mm

