## **HEAVY DUTY ENCLOSURES**

## **IP67 Low Profile Cases**

Beautifully designed low profile IP67 waterproof enclosures, ideal for tracking/monitoring in harsh environments.

• IP67 rated, perfect for outdoor applications


TAKACHI

- White enclosures made from ASA UL94-HB plastic for high ultraviolet resistance
- Dark Grey enclosures made from ABS UL94-V0 plastic for high flammability rating
- · Wall mount holes behind hinged caps for superior aesthetic finish
- Mounting kit accessory for easy mounting to poles, pillars, posts
  and lamp posts

## SPECIFICATION Material:

matoman	
Dark grey	Base & lid ABS UL94-V0
White grey	Base & lid ASA UL94-HB
Operating temperature	ABS, -10°C to +50°C ASA, -30°C +60°C
Standard colours	Dark grey or white grey
Standard unit includes	Lid, base, gasket & fixing screws





DARK GREY	WHITE GREY					
ТАКАСНІ	TAKACHI	LENGTH	WIDTH	HEIGHT		
WP5-7-2C	WP5-7-2G	65mm	52mm	18mm	NEW	
WP5-7-3C	WP5-7-3G	65mm	52mm	27mm	NEW	
WP8-8-2C	WP8-8-2G	75 <i>mm</i>	75mm	22mm	NEW	
WP8-8-4C	WP8-8-4G	75 <i>mm</i>	75mm	35mm	NEW	
WP6-8-2C	WP6-8-2G	80mm	60mm	20mm	NEW	
WP6-8-3C	WP6-8-3G	80mm	60mm	30mm	NEW	
WP8-10-2C	WP8-10-2G	100mm	75mm	22mm	NEW	
WP8-10-4C	WP8-10-4G	100mm	75mm	35mm	NEW	
WP10-10-3C	WP10-10-3G	100mm	100mm	25mm		
WP10-10-4C	WP10-10-4G	100mm	100mm	40mm		
WP9-13-3C	WP9-13-3G	130mm	90mm	25mm		
WP9-13-4C	WP9-13-4G	130mm	90mm	40mm		
WP11-15-3C	WP11-15-3G	150mm	110mm	27mm		
WP11-15-4C	WP11-15-4G	150mm	110mm	40mm		
WP13-18-5C	WP13-18-5G	175mm	130mm	45mm	NEW	
WP13-18-3C	WP13-18-3G	175mm	135mm	30mm	NEW	

Rubber Feet			
TAKACHI PART NO.	LENGTH	WIDTH	HEIGHT
PFF-M2.5D	10	10	7.5

## **Pole Mount Kit**

TAKACHI PART NO.	LENGTH	WIDTH	HEIGHT	DESCRIPTION
WPMB-M3G	18mm	14mm	9.5mm	Pole mount kit, dark grey
WPMB-M3D	18mm	14mm	9.5mm	Pole mount kit, white grey
WPMB-M4D	28mm	18mm	12mm	Pole mount kit, dark grey
WPMB-M4G	28mm	18mm	12mm	Pole mount kit, white grey

