

T 5 Ø 16 mm
E 14
16,0 x 35,0



T 5 Ø 16 mm
BA 15d
16,0 x 35,0



E 14



BA 15d

Spannung Voltage	Stromstärke Current	Leistung Power	Lichtstärke Light intensity	Lebensdauer Lifetime	Bestellcode Ordering Code	
					1635 40 ..	1635 50 ..
V	mA	Watt	MSCP	(h) AC		
12	250	3,00	1,500	3.000		1635 50 012 003
12	410	5,00	2,500	2.000		1635 50 012 005
24	83	2,00	0,800	2.000		1635 50 024 002
24	125	3,00	1,200	5.000	1635 40 024 003	1635 50 024 003
24	210	5,00	1,800	2.000	1635 40 024 005	1635 50 024 005
30	100	3,00	1,000	2.000	1635 40 030 003	1635 50 030 003
30	166	5,00	1,800	2.000	1635 40 030 005	1635 50 030 005
48	63	3,00	1,000	2.000		1635 50 048 003
48	105	5,00	1,500	2.000		1635 50 048 005
60	50	3,00	1,000	2.000	1635 40 060 003	1635 50 060 003
60	83	5,00	1,500	2.000	1635 40 060 005	1635 50 060 005
80	63	5,00	1,600	2.000		1635 50 080 005
220-260	20	3-5	0,400	2.000	1635 40 2226 35	1635 50 2226 35
220-260	23	5-7	0,500	5.000	1635 40 2226 57	1635 50 2226 57
220-260	32	6-10	1,600	5.000		1635 50 2226 61

Weitere Spannungen auf Anfrage.
Further voltages on request.

Technische Änderungen vorbehalten.
Technical changes reserved.