



TEGERA® 30



[Learn more](#)

Leather glove, unlined, 0,6-0,7 mm/23-27 mil full grain goatskin of top quality, nylon, Cat. II, reinforced index finger, for precision work

CHARACTERISTICS

- High level of protection
- Durable
- Perfect fit
- Extremely good fingertip sensitivity

FUNCTIONS

- Reinforced index finger

PREVENTS RISK OF

Abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt

PRIMARY ENVIRONMENTS OF USE

Indoors, clean environments

PRIMARY AREAS OF USE

Fine assembly, assembly, inspection work, installation work

PRIMARY INDUSTRIES OF USE

Machinery and equipment, mro, automotive

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Assembly gloves, Precision work gloves

CATEGORY Cat. II

PALM MATERIAL Full grain goatskin of top quality

BACK MATERIAL Nylon

LINING Unlined

LENGTH 220-260 mm

DEXTERITY 5

COLOUR Blue, White

PAIRS PER: BUNDLE/CARTON 12/120

DISPLAY TYPE Thread


FASTENING Elasticated 180°

OUTER MATERIAL SPECIFICATION Leather, Nylon, Natural latex

COMPLIANCE



TP TC 019:2011



EN 388:2016+A1:2018 2111X

EN ISO 21420:2020

SIZE		ARTICLE NUMBER	EAN
5	XXS	30-5	7392626027220
6	XS	30-6	7392626022850
7	S	30-7	7392626022867
8	M	30-8	7392626022874
9	L	30-9	7392626022881
10	XL	30-10	7392626022898
11	XXL	30-11	7392626022904
12	3XL	30-12	7392626035669

ejendals

Limavägen 28, SE-793 32 Leksand, Sweden
 Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com