## **ALPHA**

### 3477UFR100P62 blue

EAN 4031582305890

Swivel castor with total lock, tail end of castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, dustguard, plate fitting. Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, roller bearing





Picture may differ from original product


#### **Technical Data**

Wheel diameter	100 mm
Width of Tread	34 mm
Size of Plate	105 x 85 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Offset	41 mm
Swivel Interference	246 mm
Overall height	128 mm
Temperature	- 20 / + 80 °C
Standard	EN 12532
Weight	1.046 kg
Swivel Radius	123 mm
Hardness of tread	Shore A 64
Load capacity	160 kg
Load capacity (static)	320 kg


#### Advantages at a glance

Roll performance	• • • 0 0
Movement noise	• • • •
Attrition	• • • 0 0
Corrosion resistance	• • • 0 0

#### **Dimensions**



#### **Structure & Mounting**



# **ALPHA**

## 3477UFR100P62 blue

EAN 4031582305890

#### **Structure & Mounting**

