

Cherry Keyboard STREAM [DE] black



Manufacturer: Cherry
Art#: 2810141
Ref#: JK-8500DE-2

Details

	Keyboard
Keyboard language	German
Numeric keypad	Y
Hot keys	Y
Keyboard layout	QWERTZ
Multimedia keys	Y
Certification	cURus\nVDE-GS\nCE\nFCC
Keyboard key switch	Mechanical
Keyboard keys operating life	20 million characters
Pointing device	N
Recommended usage	Office
Device interface	USB
Keyboard form factor	Standard
Number of hot keys	10
Keyboard number of keys	105
Windows keys	Y
	Technical details
Vendor	Cherry
	Weight & dimensions
Keyboard dimensions (WxDxH)	463 x 163 x 18 mm
Keyboard weight	910 g

	Design
Product colour	Black
Backlight	N
Protection features	Splash proof
Wrist rest	N
Surface coloration	Monotone
Keyboard style	Straight
	Mouse
Mouse included	N
	Logistics data
Quantity per pallet	36 pc(s)
	Power
Power consumption	20 mA
Power source type	USB
	Operational conditions
Operating temperature (T-T)	0 - 40 °C
Storage temperature (T-T)	-20 - 60 °C
	Packaging data
Package depth	210 mm
Package height	24 mm
Package width	480 mm
Package type	Box
Number of products included	1 pc(s)
Package weight	1100 g
	System requirements
Windows operating systems supported	Y
	Ergonomics
Cable length	1.8 m

Addon Items



Cherry Slipcover WetEx for
STREAM Keyboard 105
Tasten
Artikel-Nr.: 2900002