Data sheet

testoterm measuring strips testoterm measuring points testoterm mini indicators



Self-adhesive temperature films

testoterm measuring strips testoterm measuring points testoterm mini indicators


Clear indication by irreversible colour change
within 2 to 3 seconds

Covers a large measuring range

Can be used universally

Printing of individual logo possible

Delivery on rolls possible for large orders





testoterm measuring strips and mini indicators are self-adhesive, temperature-resistant films with heat-sensitive elements for checking and monitoring temperature, e.g. for measurements on moving parts, for long-term monitoring and on small objects.

Equally suitable for checking a defined maximum temperature are the also self-adhesive and temperature-resistant testoterm measuring points with heat-sensitive elements.



testoterm measuring strips

testoterm measuring strips

testoterm measuring strips are self-adhesive films with heat-sensitive elements for checking and monitoring temperature, e.g. for measurements on moving parts, for long-term monitoring and on small objects.

- Irreversible temperature changes takes place within 2 seconds
- Practical pack with 10 testoterm measuring strips each
- 8 temperature levels



General technical data		
Accuracy	from +43 °C to +154 °C: ±1.5 °C; from +160 °C: ±1 % ±1 °C of the respective temperature value	
Operating temperature	corresponds to the respective measuring ranges	
Storage	up to +50 °C: max. 6 months from +50 °C: max. 12 months Maximum storage temperature +25 °C. Storage in refrigerator recommended.	
LxB	50 x 18 mm or 39 x 18 mm	

Available temperature ranges		
+37 to +65 °C	Order no. 0646 0108	
+71 to +110 °C	Order no. 0646 0916	
+116 to +154 °C	Order no. 0646 1724	
+161 to +204 °C	Order no. 0646 2532	
+204 to +260 °C	Order no. 0646 3341	

Discounts
Number of packs
1 to 4 packs
5 to 9 packs
10 to 19 packs
20 to 49 packs
50 to 99 packs
from 100 packs

Possible special orders: 0646 9999

Special temperature ranges

Temperature ranges	Temperature levels	Minimum order quantity	Delivery time
+29 to +40 °C	5	100 pack	7 weeks
+249 to +280 °C	5	100 pack	7 weeks
+182 to +241 °C	9	4 rolls (@ 1,000 testoterm measuring strips)	7 weeks

testoterm measuring strips on a roll

1 roll @ 1,000 testoterm measuring strips

Minimum order quantity: 4 rolls (= 4,000 testoterm measuring strips)



Individual company logo

From 10,000 off (per temperature value), the testoterm measuring strips can be printed with the company name or the company logo.

Minimum order quantity: 10 rolls (= 10,000 testoterm measuring strips)





testoterm measuring points

testoterm measuring points



testoterm measuring points are self-adhesive, temperature-resistant films with heat-sensitive elements for monitoring a defined maximum temperature.

- Irreversible temperature changes takes place within 2 seconds
- Practical pack with 50 testoterm measuring strips each
- 1 temperature level

	10.001 151.00 15.00
Accuracy	from +43 °C to +154 °C: ±1.5 °C;
	from +160 °C: ±1 % ±1 °C of the respective
	temperature value
Operating temperature	corresponds to the respective measuring
	ranges
Storage	up to +50 °C: max. 6 months
	from +50 °C: max. 12 months
	Maximum storage temperature +25 °C.
	Storage in refrigerator recommended.

Available temperature ranges		
+65 °C	Order no. 0646 1065	
+71 °C	Order no. 0646 1071	
+77 °C	Order no. 0646 1077	
+82 °C	Order no. 0646 1082	
+110 °C	Order no. 0646 1110	
+121 °C	Order no. 0646 1121	

Discounts
Number of packs
1 to 4 packs
5 to 9 packs
10 to 19 packs
20 to 49 packs
50 to 99 packs
from 100 packs

Possible special orders: 0646 9999

Special temperature ranges

Temperature ranges				Minimum order quantity	Delivery time	
+37 °C +40 °C +43 °C +46 °C +49 °C +54 °C	+60 °C +88 °C +93 °C +99 °C +104 °C +116 °C	+127 °C +132 °C +138 °C +143 °C +149 °C +154 °C	+166 °C +171 °C +177 °C +182 °C +199 °C +204 °C	+249 °C +280 °C	50 pack (= 2,500 testoterm measuring points)	7 weeks

testoterm measuring points on a roll

1 roll @ 1,000 testoterm measuring strips


Minimum order quantity: 6 rolls (= 6,000 testoterm measuring strips)

Delivery 7 weeks

Individual company logo

From 10,000 off (per temperature value), the testoterm measuring strips can be printed with the company name or the company logo.

Minimum order quantity: 10 rolls (= 10,000 testoterm measuring strips) Delivery 7 weeks





testoterm mini indicators

testoterm mini indicators

testoterm mini-indicators are adhesive, heat-resistant films with heat-sensitive elements for temperature monitoring and control.

They are particularly suitable for temperature control on small objects.

- Irreversible temperature changes takes place within 2 seconds
- Practical pack with 10 testoterm mini indicators each
- 5 temperature levels

General technical data		
Accuracy	from +43 °C to +154 °C: ± 1.5 °C; from +160 °C: ± 1 % ± 1 °C of the respective temperature value	
Operating temperature	corresponds to the respective measuring ranges	
Storage	up to +50 °C: max. 6 months from +50 °C: max. 12 months Maximum storage temperature +25 °C. Storage in refrigerator recommended.	
Diameter	15 mm	

Available temperature ranges				
+60/+65/+71/+77/+82 °C	Order no. 0646 0072			
+88/+93/+99/+104/+110 °C	Order no. 0646 0073			
+116/+121/+127/+132/+138 °C	Order no. 0646 0074			
+143/+149/+154/+160/+166 °C	Order no. 0646 0075			
+171/+177/+182/+188/+193 °C	Order no. 0646 0076			
+199/+204/+210/+216/+224 °C	Order no. 0646 0077			

Discounts	
Number of packs	
1 to 4 packs	
5 to 9 packs	
10 to 19 packs	
20 to 49 packs	
50 to 99 packs	
from 100 packs	

Possible special orders: 0646 9999				
Special temperature ranges				
Temperature ranges Minimum order quantity Delivery time				
+40/+43/+46/+49/+54 °C +232/+241/+249/+254/+260 °C	100 pack (= 1,000 testoterm mini indicators)	7 weeks		