
Thermax™ **Irreversible Temperature Sensitive Labels**

- Immediate and Permanent Record of Highest Temperature
- **Oil and Water Resistant**
- **Self Adhesive Label**
- Accuracy-Less than 100°C is ±1°C 100°C to 154°C is ±1.5°C Greater than 154°C is ±4°C
- Temperature Range 29-290°C
- Silver to Black (Below 204°C/399°F)
- Orange to Black (Above 210°C/410°F)
- Last Black Event is the Highest **Temperature Achieved**

Α	°F	99	104	109	115	120
A	°C	37	40	43	46	49
В	°F	120	129	140	149	160
D	°C	49	54	60	65	71
С	°F	171	180	190	199	210
C	°C	77	82	88	93	99
D	°F	219	230	241	250	261
	°C	104	110	116	121	127
Е	°F	270	280	289	300	309
	°C	132	138	143	149	154
F	°F	320	331	340	351	360
	°C	160	166	171	177	182
G	°F	370	379	390	399	410
G	°C	188	193	199	204	210
н	°F	421	435	450	466	480
	°C	216	224	232	241	249
	°F	480	489	500	536	554
	°C	249	254	260	280	290



5 LEVEL SPECIFICATIONS Size: 1.53" x 0.7" (39x18mm)

Type: Vertical, Self Adhesive Scale: °F and °C Range: (Sold in units of 10)

2	°F	120	130	140	150
	°C	49	54	60	65
4	°F	200	210	220	230
	°C	93	99	104	110
5	°F	240	250	260	270
	°C	116	121	127	132
7	°F	320	330	340	350
	°C	160	166	171	177
8	°F	360	370	380	390
	°C	182	188	193	199
9	°F	400	410	420	435
	°C	204	210	216	224

116121127132

4 LEVEL MICRO SPECIFICATIONS

0.15" x 0.43" (4x11mm) Size: Type: Horizontal, Self Adhesive Scale: °F or °C Range: (Sold in units of 10)

1	°F	105	110	115	120	130
	°C	40	43	46	49	54
2	°F	140	150	160	170	180
~	°C	60	65	71	77	82
3	°F	190	200	210	220	230
3	°C	88	93	99	104	110
4	°F	240	250	260	270	280
4	°C	116	121	127	132	138
5	°F	290	300	310	320	330
5	°C	143	149	154	160	166
4	°F	340	350	360	370	380
6	°C	171	177	182	188	193
7	°F	390	400	410	420	435
/	°C	199	204	210	216	224
8	°F	450	465	480	490	500
0	°C	232	241	249	254	260

5 LEVEL CLOCK

SPECIFICATIONS Size: 0.55" Dia. (14mm) Type: Circular, Self Adhesive Scale: °F and °C Range: (Sold in units of 10)



^	°F	99	104	111	115	120	129	140	144	149	160
Α	°C	37	40	44	46	49	54	60	62	65	71
В	°F	171	180	190	199	210	219	230	241	250	261
D	°C	77	82	88	93	99	104	110	116	121	127
С	°F	270	280	289	300	309	320	331	340	351	360
C	°C	132	138	143	149	154	160	166	171	177	182
D	°F	370	379	390	399	410	421	435	450	466	480
	°C	188	193	199	204	210	216	224	232	241	249

10 LEVEL SPECIFICATIONS

Size: 2.00" x 0.7" (51x18mm) Scale: °F and °C

Type: Range: (Sold in units of 10)

Vertical, Self Adhesive

Α	°F	99	104	109	115	120	129	140	149	
A	°C	37	40	43	46	49	54	60	65	
В	°F	160	171	180	190	199	210	219	230	
D	°C	71	77	82	88	93	99	104	110	
С	°F	241	250	261	270	280	289	300	309	
C	°C	116	121	127	132	138	143	149	154	
D	°F	320	331	340	351	360	370	379	390	
	°C	160	166	171	177	182	188	193	199	
Ε	°F	399	410	421	435	450	466	480	489	
	°C	204	210	216	224	232	241	249	254	1

500 260

Size: 2.00" x 0.7" (51x18mm) Scale: °F and °C

8 LEVEL SPECIFICATIONS

Type: Vertical, Self Adhesive (Sold in units of 10) Range:

1	°F	84	93	99	104	108	111
	°C	29	34	37	40	42	44
2	°F	111	115	120	129	140	144
-	°C	44	46	49	54	60	62
3	°F	149	160	171	180	190	199
3	°C	65	71	77	82	88	93
4	°F	210	219	230	241	250	261
4	°C	99	104	110	116	121	127
5	°F	270	280	289	300	309	320
3	°C	132	138	143	149	154	160
4	°F	331	340	351	360	370	379
6	°C	166	171	177	182	188	193
7	°F	390	399	410	421	435	450
7	°C	199	204	210	216	224	232
8	°F	466	480	489	500	536	554
0	°C	241	249	254	260	280	290



Horizontal, Type: Self Adhesive Scale: °F and °C Range: (Sold in units of 10)

°F	93	99	104	109	115	120	129	140	EN
°C	34	37	40	43	46	49	54	60	SP
°F	149	160	171	180	199	219	241	261	Siz
°C	65	71	77	82	93	104	116	127	5121
°F	280	300	320	340	360	380	399	421	Sca
°C	138	149	160	171	182	193	204	216	Rar
°F	450	480	500	536	554				
°C	232	249	260	280	290				Тур

Α	°F	99	111	120	129
	°C	37	44	49	54
D	°F	219	230	241	250
	℃	104	110	116	121
Е	°F	261	270	280	289
	°C	127	132	138	143
F	°F	300	309	320	331
	℃	149	154	160	166

4 LEVEL SPECIFICATIONS


Size: 0.91" x 1.77" (23x45mm) Type: Horizontal, Self Adhesive Scale: °F and °C Range: (Sold in units of 10)



nge: (Sold in units of 50) Single temperature De: indicator shows when maximum temperature has been achieved. Self adhesive.

ιx®	4 L. RA	NGE J.
260°C	280°C	290°C
FOODE	50005	EE doE
	CK AT BAT	554°F ING SHOWN
	0	





65

54

49 46

44

40

THERMAX

40

111

99