

Portable Canvio Gaming

Level Up Your Storage



4 2 1
TB TB TB

Color

Be prepared for the next game drop with the Canvio Gaming hard drive, making expanding your game library easier than ever. This Portable Hard Drive is designed to support your optimal gaming experience by freeing up room on your console so you can grow your game library along with your skills. With up to 4TB of additional storage, you can play wherever your game takes you.




2.5" 2.5" External Hard Drive

 Sleek black finish

Works with PlayStation / Xbox / PC

Store up to 25+ games per TB*

Manual

[Canvio-Gaming_UM.pdf](#) 

Tools

[ToshibaStorageDiagnosticTool_1.30.8920.zip](#) 



Product Specifications

Basic Specifications

Interface	USB 3.2 Gen 1 (USB 2.0 compatible)
Max. transfer rate	~ 5.0 Gbit/s
File system	exFAT
Power	USB bus power (max. 900mA)
System requirements	Formatted exFAT for: - Playstation/Xbox (Please check compatibility list) - Windows® 10 , Windows ® 8.1, - macOS v11.5 / v11.2, v10.15, macOS v10.14, macOS v10.13 One free port of USB Type-A

Box Content

Box Content	Canvio Gaming USB 3.2 Gen 1 cable (Type A to Micro-B) User's manual (pre-installed on the hard drive)
--------------------	---

Physical

Weight (approx.)	1 TB, 2 TB: 149g 4 TB: 210g
Dimensions	1 TB, 2 TB: 80 x 111 x 13.5 4 TB: 80 x 111 x 19.5
Enclosure	sleek black finish

Product Range

Part number	Capacity	Color
HDTX140EK3CA	4 TB	Black
HDTX120EK3AA	2 TB	Black
HDTX110EK3AA	1 TB	Black

Logistical Information:

Box dimensions	111 x 38 x 141
Box weight (gross)	1TB, 2TB: 248g 4TB: 304g
Master carton dimensions	123 x 205 x 165
Master carton weight (gross)	1TB, 2TB: 1.37kg 4TB: 1.65kg
Boxes per master carton	5
Pallet dimensions	1150 x 1150 x 130
Pallet weight (net)	22kg
Units per pallet	1350

Contact

Toshiba Electronics Europe GmbH

Hansaallee 181
40549 Düsseldorf
Germany