



Dashcams

DrivePro 10

Featuring a compact, minimalist design, Transcend's DrivePro 10 dashcam comes equipped with the STARVIS™ high-sensitivity image sensor to capture high-resolution images with extremely fine tonal gradation even in low light; a 140° wide angle lens offering the best coverage of the road; up to 1080P Full HD recording at 60fps to capture every crucial detail; Wi-Fi connectivity for live monitoring on your smart gadgets; and emergency recording for optimum protection.



Vision in the dark

The DrivePro 10 features the STARVIS™ image sensor to capture sharp, high-resolution images in superb, rich color even in low light, making it perfect for filming during both day and night. It is equipped with a 140° wide-angle lens, providing a broad field of view.

Note: STARVIS is a trademark of Sony Corporation.



Compact and discreet

The DrivePro 10 comes in a compact, discreet design that allows it to be flexibly mounted on your front or rear windshield. Being able to easily hide behind the rearview mirror out of sight, the DrivePro 10 offers the driver an unobstructed view of the road ahead or behind.



Get super smooth, detail-packed footage

Supporting 1080P Full HD recording at 60fps, the DrivePro 10 will give you footage as smooth as butter. Shooting at 60fps means you can zoom in on any shot and easily make out crucial details, such as license plates.



Dashcams DrivePro 10

Features

- STARVIS™ high-sensitivity image sensor
- 1080P Full HD recording at 60 fps
- Built-in battery prevents losing crucial images in the event of a power outage
- Emergency recording prevents overwriting of the current recorded file
- Compact design for an unobstructed view of the road ahead or behind



DrivePro App

DrivePro App is designed for use with DrivePro dashcams featuring Wi-Fi connectivity. Stream videos and adjust settings from your mobile device, and download footage for on-the-go!



DrivePro Toolbox

DrivePro Toolbox helps you play and manage videos recorded on your DrivePro dashcam without installing any separate codecs.

Specifications

Appearance

Dimensions	58.3 mm x 36 mm x 28.6 mm (2.3" x 1.42" x 1.12")
Weight	40 g (1.41 oz)

Interface

USB Type	micro USB to car lighter adapter
Connection Interface	USB 2.0
Wi-Fi Protocol	802.11n

Hardware

Image Sensor	STARVIS™
Viewing Angle	140° (diagonal)
Aperture	F/2.0

Operating Environment

Operating Temperature	-20°C (-4°F) ~ 60°C (140°F)
Storage Temperature	-25°C (-13°F) ~ 70°C (158°F)
Input Voltage	12V ~ 24V
Output Voltage	5V / 2A

Format

Resolution	Full HD 1080P
Frame Rate	60/30 fps
Video Format	MP4 (H.264)

Warranty

Certificate	CE / FCC / BSMI / NCC / MIC / KC / RCM / EAC
Warranty	Two-year Limited Warranty

Package

Package Contents	Full unit / 32GB microSD memory card / Car mount / Car lighter adapter / Quick Start Guide
------------------	--

Ordering Information

32GB	TS-DP10A-32G
------	--------------

Product specifications are subject to change without notice. Pictures shown may differ from actual products. Total accessible capacity varies depending on operating environment.