



10-Port USB Hub TU2-H10 (v1.0R)

- Add 10 USB 2.0 ports to a workstation*
- No CD installation – just plug in
- Long USB cable connection to computer
- Power adapter for power hungry connected devices
- Windows[®] and Mac[®] compatible

TRENDnet's 10-Port USB Hub, model TU2-H10, adds 10 USB 2.0 ports to a workstation. No CD installation required—simply plug in flash drives, storage enclosures, and other USB devices. The TU2-H10 works with Windows[®] and Mac[®] devices and is compatible with older USB 1.1 and 1.0 devices.

Ease of Use



Easy Setup

No CD installation – just plug in



Computer Connection

Includes a long 90 cm (35 in.) USB cable to connect to computer



Operating Systems

Compatible with Windows[®] and Mac[®] operating systems



LED Indicators

LED indicators confirm USB connectivity



Power Adapter

Provides up to 12.5 Watts of total power

Networking Solution



USB ports



USB ports



Computer



Specifications

Standards

- USB 2.0
- USB 1.1

Device Interface

- 10 x Type A USB 2.0 ports **
- 1 x Type Mini-B USB 2.0 port (computer connection)
- LED Indicators
- Power port

Maximum Data Rate

- Up to 480 Mbps

Operating Temperature

- 0 – 50 °C (32 – 122 °F)

Humidity

- Max. 90% non-condensing

Power

- Input: 100-240 V, 50/60 Hz, 0.5 A
- Output: 5 V DC 2.5 A external power adapter
- Consumption: 12.5 Watts (Max.)

Dimensions

- 156 x 74 x 20 mm (6.1 x 2.9 x 0.8 in.)

Weight

- 134 g (4.7 oz.)

Warranty

- 2 year limited

Certifications

- CE
- FCC

Package Contents

- TU2-H10
- Quick Installation Guide
- Power adapter (5 V DC, 2.5 A)
- USB cable (90 cm/35 in.)

* Not for charging iPad® tablets or other non-standard USB 2.0 chargers

** Maximum power output for a bus powered hub is up to 500 mA. Power adapter required when total power consumption exceeds 500 mA.

