



Indoor / Outdoor 4 MP Motorized Varifocal PoE IR Network Camera

TV-IP344PI (v1.1R)


- 4 MP resolution at 30 fps
- Auto-focus / optical zoom
- Night vision up to 30 m (100 ft.)
- Outdoor IP66 weather rating
- Save installation costs with Power over Ethernet (PoE)
- Program motion detection recording and email alerts
- Digital Wide Dynamic Range image balancing
- ONVIF and IPv6 support

TRENDnet's Indoor / Outdoor 4 MP Varifocal PoE IR Network Camera, model TV-IP344PI, provides powerful 4 MP HD night vision at 30 fps in complete darkness for up to 30 m (100 ft.). This IP66 weather rated camera features auto-focus / optical zoom which provides installation flexibility and time savings. Use the included pro-grade software to manage up to 32 TRENDnet cameras or download the free iOS® or Android™ mobile app.




4 MP HD Surveillance

4 MP H.264 HD Video @ 30 fps and 30 m (100 ft.) night vision provides high-resolution 24-hour surveillance.



Enhanced Viewing


Adjustable mounting base allows users to capture the precise viewing field and 4.2x optical zoom with auto-focus enhances the image to provide better detail and clarity.



Outdoor Ready

Built for extreme environments with an IP66 weather rating and an operating temperature range of -20 to 60 °C (-4 to 140 °F).

Networking Solution



- 1 10/100 Mbps PoE port
- 2 Optional power port
- 3 Speaker port
- 4 Microphone port
- 5 Grounding
- 6 GPIO
- 7 IP66 rated
- 8 IR LEDs
- 9 Motorized varifocal lens
- 10 Adjustable sun visor
- 11 Mounting bracket



4 Megapixel

Record 2688 x 1520 pixel resolution at a 30 fps in the space saving H.264 compression format



Auto-Focus / Optical Zoom

Auto-focus saves installation and troubleshooting time and remote optical zoom allows users to capture the precise desired viewing field



Night Vision

Night vision up to 30 m (100 ft.) in complete darkness



PoE

Save installation costs with Power over Ethernet (IEEE 802.3af)



Outdoor Ready

Outdoor IP66 weather rated with an operating temperature range of -20 to 60 °C (-4 to 140 °F)



Mounting Hardware

Integrated adjustable mounting bracket tilts 180 degrees and rotates 360 degrees



GPIO Ports and Alerts

Network an alarm system to Input/Output ports



Audio Support

Audio in and out ports for third party microphone and speaker (sold separately)



MicroSD Card Slot

Add up to 64 GB memory for on-board video storage



D-WDR

Digital Wide Dynamic Range improves video quality in high contrast lighting environments



Motion Detection

Create motion detection windows with separate sensitivity settings and event triggers



IPv6 / ONVIF

IPv6 supported and ONVIF compliant



Varifocal

Optical zoom by a factor of 4.2x with auto-focus to a final fixed position for installation flexibility



Multi-Language Interface

Support for English, French, Spanish, German, and Russian



Complimentary App

Live video to a mobile device with a free iOS® and Android™



Complimentary Software

Complimentary pro-grade software to manage up to TRENDnet 32 cameras

Specifications

Lens

- Focal Length: 2.8 - 12 mm @ F1.4
- Focal depth: 30 cm to infinity
- Motorized varifocal lens
- Sensor: 1/3" 4 Megapixel CMOS sensor
- Zoom: optical 4.2x, digital 4x

Viewing Angle

- Diagonal: 40 - 117°
- Horizontal: 36 - 103°
- Vertical: 19 - 56°

Minimum Illumination

- IR off: 0.031 lux
- IR on: 0.08 lux
- 30m IR illumination distance
- IR wavelength: 850nm

Video Codecs / Resolution

- H.264: 2688 x 1520 up to 30 fps
- MJPEG: 2688 x 1520 up to 30 fps
- H.264: 640 x 480 up to 15 fps (3GPP only)

Audio

- 3.5 mm microphone jack
- 3.5 mm speaker jack

Standards

- IEEE 802.1x
- IEEE 802.3
- IEEE 802.3u
- IEEE 802.3x
- IEEE 802.3af

Device Interface

- 10/100 Mbps PoE port
- Micro SD card slot
- IR LEDs
- 3.5 mm microphone jack
- 3.5 mm speaker jack
- GPIO terminal
- Power jack

Housing

- IP66 rated
- Adjustable sun visor
- Adjustable mounting bracket can pivot 180 and rotate 360 degrees

Network Protocol

- IPv4, IPv6, UDP, TCP / IP, ONVIF V2.4.2
- DHCP, NTP, DDNS, SMTP, FTP, LLTD
- SNMP v1-v3, QoS / DSCP, IEEE 802.1X
- Samba, Bonjour
- HTTP, HTTPS
- PPPoE
- UPnP, RTSP, RTP, 3GPP

Dimension

- 77 x 77 x 205 mm (3.0 x 3.0 x 8.1 in.)

Weight:

- 688 g (1.5 lbs.)

Operating Temperature

- -20 – 60 °C (-4 – 140 °F)

Humidity

- Max. 90% non-condensing

Power (optional not included)

- Input: 100 - 240 V AC , 50 - 60 Hz, 1 A
- Output: 12 V DC 1 A external power adapter (for non-PoE installations)
- Max Consumption: 8.64 W

Management Interface

- Multi-language support: English, French, German, Russian, and Spanish
- IP address filter
- QoS traffic prioritization
- Time, date, and text overlay
- Image settings: brightness, contrast, hue, sharpness, D-WDR, Denoise 2D, Shutter time, sense-up, Saturation, , AGC (automatic gain control), flip, mirror, 90 degree rotate, IR, day / night mode, white balance
- D-WDR enhances video quality in high contrast daytime lighting
- 2D Digital Noise Reduction enhances night vision quality
- Recording: to computer, NAS, SAMBA, or through software
- Video Recording: scheduled, motion detection, sound detection, and tamper detection
- Motion detection: define up to three motion detection areas and motion sensitivity

- Sound detection: requires installation of third party microphone
- Privacy masks: define custom privacy mask up to 3 areas
- Tamper detection function: email notification, FTP, alarm, SD card, or Samba server if the viewing field darkens suddenly
- Network disconnection fallback: set to automatically save video to Micro SD card (sold separately) if connection to network is broken
- Snapshot: real time snapshot, sound detection, and motion detection
- Supported dynamic DNS services: dyn.com, no-ip.com, and iptecno.com
- Management setting: maximum 21 user accounts
- Supports remote management
- Compatibility (PC based): Internet Explorer® 8.0 or higher

TRENDnetVIEW Pro Software

- Supports up to 32 TRENDnet cameras
- Multiple language support
- Set recording options (motion detection, schedule, event trigger)
- Advanced search and playback tools
- Custom viewing modes and options
- Compatibility: Windows® 10, 8.1, 8, 7, Vista, XP, Windows Server® 2003, 2008

TRENDnetVIEW App

- Free iOS™ and Android™ app
- View the camera on a mobile device
- Take snapshots
- Zoom

Certifications

- CE
- FCC

Warranty

- 3 year limited

Package Contents

- TV-IP344PI
- Quick Installation Guide
- CD-ROM (Utility, Software, & User's Guide)
- Camera mounting hardware