



Indoor 2 MP 1080p WDR Mini Pan / Tilt PoE IR Network Camera

TV-IP410PI (v1.0R)

- 2 MP 1080p HD resolution
- Night vision up to 10 m (32.8 ft.)
- Increase bandwidth efficiency with H.264+ video compression
- Save installation costs with Power over Ethernet (PoE)
- Digital Wide Dynamic Range image balancing
- Program motion detection recording and email alerts
- MicroSD card slot (up to 128 GB)
- ONVIF and IPv6 support
- Free iOS® and Android™ mobile apps

TRENDnet's Indoor 2 MP 1080p WDR Mini Pan / Tilt PoE IR Network Camera, model TV-IP410PI, provides day and night surveillance with a night vision range of up to 10 meters (32.8 ft.) This mini pan / tilt network camera features adjustable wide dynamic range (WDR) image balancing that enhances image quality and clarity when exposed to high contrast lighting environments. Record 1080p video (1920 x 1080) at 30 fps in a space saving H.264+ compression format. Manage up to 32 TRENDnet cameras with included complimentary software and mobile apps.




Pan / Tilt

Motorized 180° pan and 75° tilt offers greater visibility over the environment and can be remotely controlled over the internet.



Power over Ethernet (PoE)

PoE offers cost savings, and the flexibility to install this mini pan / tilt camera in the desired location.



Wide Dynamic Range (WDR)

Adjustable wide dynamic range (WDR) image balancing that enhances image quality and clarity when exposed to high contrast lighting environments.

Networking Solution



- ❶ Optional power jack
- ❷ 10/100 Mbps PoE port
- ❸ Motorized Pan / Tilt
- ❹ Smart IR
- ❺ Micro SD card slot



2 Megapixel

Record 1080p (1920 x 1080) HD video at 30 fps in space saving H.264+ compression format



Night Vision

Night vision up to 10 meters (32.8 ft.)



Smart IR

Dynamic IR LED adjustment optimizes night visibility by varying intensity based on object distance



PoE

Save installation costs with Power over Ethernet (PoE)



Storage

Record video to a network storage device or to a micro SD card (up to 128 GB, not included).



Advanced Playback

Advanced in-camera archived video review functionality



Motion Detection

Create custom motion detection zones to record video and send email notifications when a zone is triggered.



Tamper Detection

Create custom tamper detection zones to send an email notification when the camera view has been obstructed.



Digital Wide Dynamic Range (D-WDR)

Adjustable D-WDR setting improves image quality and clarity when a camera is exposed to high contrast lighting environments by enhancing the dark areas of the image to make them more visible.



Recording Flexibility

Define custom schedules using continuous (24/7) and / or event based recording modes.



IPv6

IPv6 support



ONVIF / PSIA

ONVIF Profile S, Profile G and PSIA compliant



Complimentary Software

Complimentary pro-grade software to manage up to 32 TRENDnet cameras



Complimentary Apps

Live video to a mobile device with free iOS[®] and Android[™] apps

Specifications

Camera <ul style="list-style-type: none">• Focal Length: 2.8 @ F2.0• Sensor: 1/2.8" CMOS sensor• DNR: 3D DNR• WDR: 120 dB• Mount: M12	<ul style="list-style-type: none">• UPnP, RTSP, RTP• ONVIF Profile S, Profile G, PSIA	<ul style="list-style-type: none">• Tamper detection function: email notification, FTP, SD card, or Samba server if the viewing field darkens suddenly• Network disconnection fallback: set to automatically save video to Micro SD card (sold separately) if connection to network is broken• Snapshot: real time snapshot, sound detection, and motion detection• Supported dynamic DNS services: dyn.com, no-ip.com, and iptecno.com• Management setting: maximum 21 user accounts• Supports remote management• Compatible browsers: Chrome™ or Firefox® (live view resolution up to 640 x 360), Internet Explorer® or Safari® (live view resolution up to 1920 x 1080)
Viewing Angle <ul style="list-style-type: none">• 109.4°	Dimension <ul style="list-style-type: none">• 120 x 87 mm (4.7 x 3.4 in.)	
Pan/Tilt Rotation <ul style="list-style-type: none">• Pan: -90 ~ 90°• Tilt: 0 ~ 75°	Weight <ul style="list-style-type: none">• 500 g (1 lb.)	
Minimum Illumination <ul style="list-style-type: none">• IR off: 0.01 lux• IR on: 0 lux• 10m distance• IR wavelength : 850nm	Operating Temperature <ul style="list-style-type: none">• -10 – 40 °C (-14 – 104 °F)	
Resolution <ul style="list-style-type: none">• H.264/H.264+: 1920 x 1080 up to 25 fps• H.264/MJPEG: 640 x 360 up to 30 fps	Humidity <ul style="list-style-type: none">• Max. 95% non-condensing	
Hardware Standard <ul style="list-style-type: none">• IEEE 802.3• IEEE 802.3u• IEEE 802.3af	Power <ul style="list-style-type: none">• Input: PoE• Consumption: 5W avg. (7W IR on, 9W P/T on)	
Device Interface <ul style="list-style-type: none">• 10/100 Mbps PoE port• Micro SD card slot• IR LEDs• Power jack	Power (Power adapter not included) <ul style="list-style-type: none">• Input: 100 - 240 V AC , 50/60 Hz, 1 A• Output: 12 V DC, 1 A external power adapter (for non-PoE installations)	TRENDnetVIEW EVO Software <ul style="list-style-type: none">• Supports up to 32 TRENDnet cameras• Multiple language support• Set recording options (motion detection, schedule, event trigger)• Search and playback• Custom viewing modes and options• Compatibility: Windows® 10, 8.1, Windows Server® 2012, 2008
Micro-SD slot <ul style="list-style-type: none">• Supports Micro SD/SDHC/SDXC• Up to 128GB	Management Interface <ul style="list-style-type: none">• Multi-language support: English, French, German, Spanish and Portuguese• IP address filter• QoS traffic prioritization• Time, date, and text overlay• Image settings: brightness, contrast, hue, sharpness, Denoise 3D, Shutter time, sense-up, Saturation, AGC (automatic gain control), flip, day/night mode, white balance• WDR enhances video quality in high contrast daytime lighting• 2D Digital Noise Reduction enhances night vision quality• Recording: to computer, NAS, SAMBA, or through software• Video Recording: scheduled, motion detection, sound detection, and tamper detection• Motion detection: define up to three motion detection areas and motion sensitivity• Privacy masks: define custom privacy mask up to 3 areas	TRENDnet IPVIEW App <ul style="list-style-type: none">• Free iOS® and Android™ apps• View live camera video on a mobile device• Take snapshots• Zoom
Network Protocol <ul style="list-style-type: none">• IPv4, IPv6, UDP, TCP / IP, ONVIF, SPIA• DHCP, NTP, DDNS, SMTP, FTP, LLTD• SNMP v1-v3, QoS / DSCP, IEEE 802.1X• NFS, SMB/CIFS, Bonjour• HTTP, HTTPS• PPPoE		Certifications <ul style="list-style-type: none">• CE• FCC Warranty <ul style="list-style-type: none">• 3 year Package Contents <ul style="list-style-type: none">• TV-IP410PI• Quick Installation Guide• CD-ROM (Utility, Software, & User's Guide)• Camera mounting hardware

