

Drawer unit 45

Centrally locked high quality steel drawer units for storage of tools and small components. Mounted under workbenches with brackets. Also available with castors as a trolley version. Drawer units are epoxy powder coated in grey, RAL 7035. Central locking. Full width drawer handle in anodised aluminium. Smooth and quiet

telescopic ball-race runners with 100 % opening of the drawers. Load-bearing capacity is 60 kg per drawer. Our drawer units are suitable for use in EPAs. The mobile trolleys are available in both ESD and non-ESD versions. New drawer divider sets are available for functional and organized storage space (p. 99).



Choose the drawer unit according to your needs; with castors, plinth or no plinth.

Load capacity 150 kg, 4 swivel castors (ø 100 mm), 2 with brakes. The trolley version comes with a rubber mat that stops items from sliding on the surface.

Combination name

45/56-1
Width Height Version



The maximum load capacity of 100% extendable drawers is 60 kg!

Drawer unit 45/56, 100% opening, load capacity 60 kg/drawer

| | 45/56-1 | 45/56-2 | 45/56-3 | 45/56-4 | 45/56-7 | 45/56-10 | 45/56-11 |
|---------------------------|-------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|
| Standard | 606 49 101 | 606 49 102 | 606 49 103 | 606 49 104 | 606 49 107 | 606 49 110 | 606 49 111 |
| With plinth | 606 49 201 | 606 49 202 | 606 49 203 | 606 49 204 | 606 49 207 | 606 49 210 | 606 49 211 |
| With castors | 606 49 301 | 606 49 302 | 606 49 303 | 606 49 304 | 606 49 307 | - | - |
| Height (mm) of the drawer | 5 x 100 | 2 x 100 2 x 150 | 3 x 100 1 x 200 | 1 x 100 2 x 200 | 2 x 150 1 x 200 | 2 x 100 1 x 300 | 1 x 200 1 x 300 |

Internal drawer dimensions: 380 x 500 x 90/140/190/290 mm.

Drawer unit 45/66, 100% opening, load capacity 60 kg/drawer

| | 45/66-1 | 45/66-2 | 45/66-3 | 45/66-4 | 45/66-5 | 45/66-6 | 45/66-7 |
|---------------------------|-------------|----------------------------|---|-------------|----------------------------|----------------------------|-------------|
| Standard | 607 49 101 | 607 49 102 | 607 49 103 | 607 49 104 | 607 49 105 | 607 49 106 | 607 49 107 |
| With plinth | 607 49 201 | 607 49 202 | 607 49 203 | 607 49 204 | 607 49 205 | 607 49 206 | 607 49 207 |
| With castors | 607 49 301 | 607 49 302 | 607 49 303 | 607 49 304 | 607 49 305 | 607 49 306 | 607 49 307 |
| Height (mm) of the drawer | 6 x 100 | 3 x 100 2 x 150 | 1 x 100 2 x 150 1 x 200 | 4 x 150 | 4 x 100 1 x 200 | 2 x 100 2 x 200 | 3 x 200 |

Internal drawer dimensions: 380 x 500 x 90/140/190 mm.