

# Acer XR2 series

# Acer XR342CKPbmiiqphuzx

## Everything at a glance

Get the best entertainment experience with the huge Curved Display that seamlessly adapts to the natural shape of your eyes by creating the same distance from every corner of the screen to your eyes. The wider field of vision creates a uniquely appealing atmosphere.

The elegant metal body with a brushed design gives the Acer XR2 series a luxurious and outstanding look. To complete the bundle, it features a display with IPS technology to display true-to-life color and images in detail with 100% coverage of the sRGB color space. Multitasking is no longer a big deal thanks to picture-by-picture (PBP) and picture-in-picture (PIP) technology. Due to height adjustment and a tilt angle of -5 ° ~ 35 °, the Acer XR2 series is flexible applicable.



- Diagonal size: 86.4 cm (34.0 inches)
- Resolution (native): 3,440 x 1,440
- Response time: 1 ms
- Brightness: 300 cd/m<sup>2</sup>
- Connectivity: HDMI, DP, USB Hub, Audio Out











### Acer XR342CKPbmiiqphuzx

#### **SPECIFICATIONS**







#### Technical specifications

86.4 cm (34.0 inches) Diagonal size Active display area (WxH) 796 x 333 mm Resolution (native) 3,440 x 1,440 Aspect ratio 21:9 Pixel pitch (PPI) 0.232 mm (109.7)

IPS Technology Panel type Response time 1 ms Brightness 300 cd/m<sup>2</sup> Backlight type LFD Acer CrystalBrite

No, anti-glare display 178°/178° Viewing angle (h/v) CR>10:1 178°/178° Viewing angle (h/v) CR>5:1 1000:1 Static contrast ratio 100M:1 Dynamic contrast ratio 1.07B Colors 100% sRGB Color space Speaker 2 x 7 watts

Connectivity HDMI, DP, USB Hub, Audio Out Yes (Power output: 60 watts) HDMI:30-160kHz / 30-100Hz, USB Type C Frequency (H/V) DP:160-160kHz / 48-100Hz, Type-C:30-160kHz / 30-100Hz

Refresh rate (max.)

#### Power supply and consumption

Min On 56 W Sleep 0.50 W Off/Standby 0.40 W Energy Efficiency Class 95 kWh Annual Energy Consumption

#### ErgoStand

Tilt angle -5°~35° +/-30° Swivel angle Height adjust range 130 mm VESA wall mounting 100x100 mm

#### Norms and Standards

Certification MPR-II MTBF 30,000 h at 25°C

#### Dimensions and weight

Container loading (20'/40')

Dimension (W x H x D) 816 x 435.5 - 565.5 x 309 mm 124.60 mm Min. thickness without stand 9.70 kg Weight (unpacked) Weight (packed) 16.30 kg Pallet qty and size ( $H \times W \times D$ ) 9 Pcs (191.2 x 96.0 x 114.0 cm)

108/216

#### Others

No Storage ambient temperature

#### Ordering Informations

XR342CKPbmiiqphuzx Model UM.CX2EE.P01 Part number EAN 4713883426121