



# Acer Business Series

## Acer B276HULCymiidprzx

*Flexible viewing, professional style*

The Acer Business Series is a powerful professional monitor series that offers top ergonomics and versatile productivity. It is designed for professionals who require exceptional visuals and comfortable viewing. The Acer Business Series has non-glare screen with white LED Technology that ensures exceptional reliability, great and better performance.



- Diagonal size: 68.6 cm (27.0 Zoll)
- Resolution (native): 2,560 x 1,440
- Response time: 6 ms
- Brightness: 350 cd/m<sup>2</sup>
- Connectivity: DVI, HDMI, DP, USB Hub, Audio Out





## Acer B276HULCymiidprzx

## SPECIFICATIONS



### Technical specifications

Diagonal size	68.6 cm (27.0 Zoll)
Active display area (WxH)	597 x 336 mm
Resolution (native)	2,560 x 1,440
Aspect ratio	16:9
Pixel pitch (PPI)	0,233 mm (108,8)
Panel type	IPS Technology
Response time	6 ms
Brightness	350 cd/m <sup>2</sup>
Backlight type	LED
Acer CrystalBrite	No, anti-glare display
Viewing angle (h/v) CR>10:1	178°/178°
Viewing angle (h/v) CR>5:1	178°/178°
Static contrast ratio	1000:1
Dynamic contrast ratio	100M:1
Colors	1,07B
Color space	100% sRGB
Speaker	2 x 2 Watt
Connectivity	DVI, HDMI, DP, USB Hub, Audio Out
Chassis colour	Darkgrey Matt
Frequency (H/V)	DVI / HDMI:31-90KHz / 56-76Hz, DP / MiniDP:113-113KHz
Refresh rate (max.)	60 Hz

### Power supply and consumption

Power supply	Internal
Electrical voltage	100/120 V AC; 220/240 V AC; 50/60 Hz
Min On	28.44 W
Sleep	0.36 W
Off/Standby	0.25 W
Energy Efficiency Class	B
Annual Energy Consumption	58 kWh

### ErgoStand

Tilt angle	-5°~35°
Swivel angle	+/-60°
Height adjust range	150 mm
VESA wall mounting	100x100 mm

### Norms and Standards

Guarantee	36 Months Carry In
Certification	TCO 6.0, CE, GS, ISO 9241-307
MTBF	30,000 h at 25°C

### Dimensions and weight

Dimension (W x H x D)	611 x 394.0 - 544.0 x 247 mm
Min. thickness without stand	21.70 mm
Weight (unpacked)	8.40 kg
Package Dimensions	20.40 x 50.50 x 69 cm
Weight (packed)	10 kg
Pallet qty and size (H x W x D)	40 St. (222.0 x 110.0 x 130.0 cm)
Container loading (20'/40')	320 / 720

### Others

Control panel	On/Off, Auto/Exit, left/right (</>), Menue/Enter, e-Key
OSD languages	EN, DE, ES, NL, FR, IT, FI, RU
Operating ambient temperature	0°C to 40°C
Operating ambient humidity	20% to 80%
Storage ambient temperature	-20°C to 65°C

### Ordering Information

Model	B276HULCymiidprzx
Product line	Acer Business Series
Part number	UM.HB6EE.C05
EAN	4713392498411