



Acer Touch Series

Acer T272HULbmidpcz

Award-winning touch technology

Don't just watch the Screen. Touch it. Control it. Interact with the modern monitors of the Acer T2 Series. The multitouch function and the great digital connectivity are combined with style to create the ultimate touch experience. The ergonomic design also allows to navigate comfortably.



- Diagonal size: 68.6 cm (27.0 Zoll)
- Resolution (native): 2,560 x 1,440
- Response time: 5 ms
- Brightness: 350 cd/m²
- Connectivity: DVI, HDMI, DP, USB Hub



Acer T272HULbmidpcz

SPECIFICATIONS



Technical specifications

Diagonal size	68.6 cm (27.0 Zoll)
Active display area (WxH)	597 x 336 mm
Resolution (native)	2,560 x 1,440
Aspect ratio	16:9
Pixel pitch (PPI)	0,233 mm (108,8)
Panel type	IPS Technology
Response time	5 ms
Brightness	350 cd/m ²
Backlight type	LED
Acer CrystalBrite	Ja
Viewing angle (h/v) CR>10:1	178°/178°
Viewing angle (h/v) CR>5:1	178°/178°
Static contrast ratio	1000:1
Dynamic contrast ratio	100M:1
Colors	16.7M
Color space	100% sRGB
Speaker	2 x 2 Watt
Connectivity	DVI, HDMI, DP, USB Hub
Frequency (H/V)	15-99kHz / 23-76Hz
Refresh rate (max.)	60 Hz

Power supply and consumption

Min On	32 W
Sleep	0.49 W
Off/Standby	0.45 W
Energy Efficiency Class	A
Annual Energy Consumption	44 kWh

ErgoStand

Tilt angle	10°~60°
VESA wall mounting	100x100 mm

Norms and Standards

Certification	MPR-II
MTBF	50,000 h at 25°C

Dimensions and weight

Dimension (W x H x D)	660 x 493 x 50 mm
Min. thickness without stand	38 mm
Weight (unpacked)	6.60 kg
Package Dimensions	74.40 x 59 x 13.20 cm
Weight (packed)	10 kg
Pallet qty and size (H x W x D)	42 St. (189.8 x 115.0 x 129.0 cm)
Container loading (20'/40')	336 / 756

Others

Storage ambient temperature	Nein
-----------------------------	------

Ordering Information

Model	T272HULbmidpcz
Part number	UM.HT2EE.009
EAN	4712196954130