

Electronic housing - UM 72-PROFIL 100CM - 2907583

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

Panel mounting base open, Lower part, Cross connection: without bus connector, Color: green, Width: 1000 mm, Length: 1000 mm, Number of positions cross connector: not relevant, Note: required profile length = PCB length - 3.6 mm



The illustration shows the variant UM 45-Profil CM

Why buy this product

- ☑ Lateral elements with potential ground contact available from the PCB to the DIN rail (EMC)
- Fast assembly on standard NS 35 or NS 32 DIN rails
- ☑ Inexpensive as a result of reducing the number of separate housing parts
- ☑ Wide range of options for external conductor connection
- ✓ Flexible size and shape
- High degree of mechanical stability by screwing the lateral elements to the profile
- The modules can be marked with Phoenix Contact marking material using the marking grooves in the press-drawn section

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	4 017918 365394
GTIN	4017918365394
Weight per Piece (excluding packing)	400.000 g
Custom tariff number	39162000
Country of origin	Germany

Technical data

General

Housing type	Panel mounting base
Housing material	PVC
Color	green

Ambient conditions

Ambient temperature (operation)	-15 °C 50 °C
---------------------------------	--------------



Electronic housing - UM 72-PROFIL 100CM - 2907583


Technical data

Dimensions

Length	1 m	
Width	1000 mm	
Technical data		
Flammability rating according to UL 94	V0	
Standards and Regulations		
Flammability rating according to UL 94	V0	
Environmental Product Compliance		
China RoHS	Environmentally friendly use period: unlimited = EFUP-e	
	No hazardous substances above threshold values	

Drawings

Dimensional drawing



Phoenix Contact 2017 © - all rights reserved http://www.phoenixcontact.com