

US75 PCIe Gen 4x4 M.2 SSD

Empowering Productivity with Advanced Storage

Features

- Boost Performance with Gen 4x4 NVMe
- Store more with the full capacities up to 4TB
- Compact M.2 2280 small form factor
- Monitor SSD Health with SP Toolbox

Specifications

Capacity	500GB, 1TB, 2TB, 4TB
Dimensions	22.0mm x 80.0mm x 3.6mm
Weight	8g
Sequential Read/Write (max.)	Up to 7,000 / 6,500MB/s
Interface	PCle Gen 4x4
Shock Resistance Test	1500g/0.5ms
MTBF (est.)	1,500,000 hours
Operating Temperature	0°C - 70°C
Certification	CE, FCC, UKCA, BSMI, Green dot, WEEE,
	RoHS, KCC
Warranty	5-year limited warranty
System Requirement	Computer with M.2 slot supporting PCle
	interface and an OS with NVMe support

^{*}Performance read/write varies by system performance (such as hardware, software, and interface mode) and capacity



Ordering Information

Capacity	Part Number
500GB	SP500GBP44US7505
1TB	SP01KGBP44US7505
2TB	SP02KGBP44US7505
4TB	SP04KGBP44US7505