

## 3m USB 3.0 Active Extension Cable - M/F

**Product ID:** USB3AAEXT3M



The USB3AAEXT3M, 3-meter Active USB 3.0 Extension Cable, offers one USB type-A (male) connector and one USB type-A (female) connector, and provides an active extension of USB 3.0 devices of up to 3-meters (10-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations; the active USB 3.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the typical length limits of standard USB cables. Up to 4 of these cables can be daisy-chained together, allowing the connection to be extended a total of 12-meters. If necessary, the USB device can be powered from a wall outlet, using the Universal AC power adapter provided with the cable.

The USB3AAEXT3M extension cable (USB Extender) supports high speed USB 3.0 transfer rates of up to 5Gbps, and is backed by StarTech.com's 2-year Warranty.

## Certifications, Reports and Compatibility

### Applications

- Cascade up to 4 levels
- Backwards compatible with USB 2.0/1.1 devices
- Extend the distance of USB peripherals beyond the USB 3.0 3-meter limitation

### Features

- Fully shielded for error-free connections
- USB bus-powered

- Plug-and-play, no driver required
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Universal external power source also included
- Compatible with PC Windows 8/7/Vista/XP and Mac computer systems

---

**Hardware**

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

---

**Connector(s)**

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	USB Type-A (9 pin) USB 3.0 (5 Gbps)

---

**Special Notes / Requirements**

Note	Cascade up to 4 USB3AAEXT3M devices together for further extension
------	--------------------------------------------------------------------

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	10

---

**Physical Characteristics**

Color	Black
-------	-------



Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	8.1 oz [230.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	9.3 in [23.5 cm]
Package Width	5.8 in [14.8 cm]
Package Height	2.0 in [52.0 mm]
Shipping (Package) Weight	10.8 oz [305.0 g]

---

**What's in the Box**

Included in Package	3 m USB 3.0 Active Extension Cable - M/F
	Universal Power Adapter
	Plug Adapters for North America, UK, Europe, and Australia

---

***\*Product appearance and specifications are subject to change without notice.***

