

USB 3.0 to SATA or IDE Hard Drive Adapter / Converter

Product ID: USB3SSATAIDE



The USB3SSATAIDE USB 3.0 to IDE/SATA Adapter Cable connects any standard 2.5in or 3.5in SATA or IDE hard drive to a computer through an available USB 3.0 Port (Backward compatible with USB 2.0). The adapter lets you connect a bare drive with no enclosure, saving time and hassle.

The USB 3.0 SATA/IDE Adapter lets you externally connect a bare drive with no drive enclosure or HDD dock required, and features LED indicators that allow you to easily monitor status and activity updates.

The adapter cable works with Windows, Linux, and Mac computers and does not require any software or driver installation - a true plug-and-play solution for adding cost-effective external storage, or overcoming incompatibility between all hard drives and USB enabled motherboards that may not be SATA or IDE-equipped.

Backed by our 2-year warranty, the USB3SSATAIDE USB 3.0 to IDE/SATA Adapter Cable comes complete with universal adapter and power cords, providing the additional power required to connect 3.5-inch and larger capacity 2.5-inch hard drives.

Certifications, Reports and Compatibility

Applications

- Service technicians who need to test or retrieve data from old hard drives
- Technicians who travel and deal with many different types of hard drives
- Connect your 2.5" and 3.5" drives to almost any notebook or desktop
- Ideal for testing and quickly swapping drives
- Easily connect and access data from a 2.5in or 3.5in hard drive with USB 3.0



• Retrieve data from a hard drive without having to connect the drive internally

Features

- Built in connectors for both 2.5in and 3.5in SATA Hard Drives (HDDs) and SATA Solid State Drives (SSDs) and IDE hard drives
- LED indicators provide status and activity updates
- Maximum transfer rate of 5Gbps using USB 3.0; 480Mbps with USB 2.0
- Compact, portable form factor
- Compliant with USB specification Rev 2.0 and 3.0
- Hot swap and plug and play compatible

н	а	rd	w	ıa	r٥

Warranty 2 Years

SATA & IDE Interface

Bus Type **USB 3.0**

Number of Drives

Drive Size 2.5in & 3.5in

Compatible Drive Types SATA & IDE

Chipset ID Innostor - IS611

Performance

Maximum Data Transfer 4.8 Gbps

Rate

Type and Rate USB 3.0 - 4.8 Gbit/s

Hardware Raid

Supported

No

ATAPI Support Yes

MTBF 35,000 hours

Connector(s)

Drive Connectors IDE (40 Pin, EIDE/PATA)



IDE (44 Pin, EIDE/PATA, 2.5" HDD)

LP4 (4 pin; Large Drive Power)

SATA (7 pin, Data)

SATA Power (15 pin)

Host Connectors USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility OS independent; No software or drivers required

Special Notes / Requirements

Note Backwards compatible with USB 1.1 standard, but not recommended

due to slow transfer rate.

Indicators

LED Indicators USB Link

IDE Detect/Activity

SATA Detect/Activity

Power

Power Source AC Adapter Included

Output Current 2A

Environmental

Operating Temperature 0C to 50C (32F to 122F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 5% ~ 85% RH

Physical Characteristics

Color Black

Material Plastic

Product Length 2.8 in [70 mm]

Product Width 1.7 in [43 mm]



Product Height 0.7 in [18 mm]

Weight of Product 2.0 oz [58 g]

Packaging Information

Package Length 5.9 in [15 cm]

Package Width 8.5 in [21.5 cm]

Package Height 2.0 in [52 mm]

Shipping (Package)

Weight

14.8 oz [419 g]

What's in the Box

Included in Package USB 3.0 to SATA/IDE converter

power adapter breakout cable

universal power adapter (NA/JP, UK, EU, AU)

SATA data cable

instruction manual

^{*}Product appearance and specifications are subject to change without notice.