

| |
|--------------------------------------|
| UT200 Series |
| 400-600A Digital Clamp Meters |
| UT201 UT202 UT202A |

| |
|---------------------|
| Introduction |
| |
| |

| |
|-----------------------|
| Safety Rating |
| CAT II 600V |
| CAT III 300V |
| Certifications |
| CE |
| EN:61010-1 |
| EN:61326-1 |
| EN:61010-2-032 |

| | | | | |
|-----------------------|-----------------------------------|-----------|-----------|-----------|
| Specifications | | | | |
| Model | | UT201 | UT202 | UT202A |
| AC Current (A) | 2A/20A/200A/400A 20A/200A/600A | ±(1.5%+5) | ±(1.5%+5) | ±(1.5%+5) |
| AC Voltage (V) | 2V/20V/200V/600V | ±(1.2%+5) | ±(1.2%+5) | ±(1.2%+5) |
| DC Voltage (V) | 200mV/2V/20V/200V/600V | ±(0.8%+1) | ±(0.8%+1) | ±(0.8%+1) |
| Resistance (Ω) | 200Ω/2KΩ/20KΩ/200KΩ/2MΩ/20MΩ | ±(1%+2) | ±(1%+2) | ±(0.8%+3) |
| Temperature (°C) | -40°C ~ 1000°C | | ±(1%+3) | |
| Temperature (°F) | -40°F ~ 1832°F | | ±(1%+6) | |

| | | | | |
|-------------------------|-------------|------|------|------|
| Features | | | | |
| Display Count | | 2000 | 2000 | 2000 |
| Auto Range | | √ | √ | |
| Manual Range | | | | √ |
| Jaw Capacity | | 28mm | 28mm | 28mm |
| Diode | | √ | √ | √ |
| Auto Power Off | | √ | √ | |
| Continuity Buzzer | | √ | √ | √ |
| Low Battery Indication | | √ | √ | √ |
| Data Hold | | √ | √ | √ |
| MAX Mode | | √ | √ | √ |
| MIN Mode | | | | √ |
| Full Icon Display | | √ | √ | |
| Input Impedance for DCV | Around 10MΩ | √ | √ | √ |

| | |
|-------------------------------|--|
| General Characteristic | |
| Power | UT201/UT202 -1.5V Batteries (R03) x2, UT202A -9V Battery (6F22) |
| LCD Size | 35.6mm X 18 mm |
| Product Color | Red and Grey |
| Product Net Weight | 220g |
| Product Size | 210mm X 75.6mm X30 mm |
| Standard Accessories | UT201/UT202A -Batteries, Test Lead, Carrying Bag UT202 -Battery, Test Lead, Carrying Bag, Point Contact Temperature Probe |
| Standard Individual Packing | Gift Box, English Manual |
| Standard Quantity Per Carton | 40 PCs |
| Standard Carton Measurement | 540mm X 495mm X 335mm (0.09 CBM Per Standard Carton) |
| Standard Carton Gross Weight | 23Kg |