

Automation Products - u-view UV66-ADV-7-CAP-W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Convenient multi-touch panels make it easy to monitor and control machines and systems. u-view multi-touch panels from Weidmüller offer excellent image quality and can be used in an industrial environment without any restrictions. The u-view series is made up of two different product lines. The basic product line features resistive multi-touch panels with a diagonal of 4.3", 7", or 10.1"; and the advanced line features capacitive multi-touch panels with a diagonal of 7", 10.1", or 15.6". All panels are equipped with a Linux operating system including HTML5 browser. As a result, they support all web-based visualisations as well as "u-control" with web engineering. The panels have a particularly flat design, with a robust aluminium IP66 housing.

Strong performance

First-class image quality and powerful processors make working with u-view multi-touch panels particularly enjoyable.

High compatibility

u-view multi-touch panels can be used in a wide variety of applications thanks to their state-of-the-art web technology based on HTML5.

Attractive design

All u-view multi-touch panels come with particularly flat and space-saving aluminium housings.

General ordering data

Type	UV66-ADV-7-CAP-W
Order No.	2555830000
GTIN (EAN)	4050118566192

**Automation Products - u-view
UV66-ADV-7-CAP-W**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	204 mm	Width (inches)	8.031 inch
Height	147.6 mm	Height (inches)	5.811 inch
Depth	40 mm	Depth (inches)	1.575 inch
Net weight	1,400 g		

Temperatures

Operating temperature	0 °C ... +50 °C	Storage temperature	-20 °C ... +60 °C
-----------------------	-----------------	---------------------	-------------------

System data

Interface	2 x Ethernet 10/100/1000 MBit (RJ45), 2 x USB 2.0 (host), 1 x serial RS-232/RS-485/ RS-422, 1 x plug-in	Memory (Flash)	4 GB
Operating system	Linux + Browser (HTML5)	Processor	ARM Cortex A9 1 GHz NXP® i.MX6 DualLite
RAM	1 GB		

Equipment

Luminance	500 cd/m ²	Material display	Glass
Material frame	metal	Number of displayable colours	16 M
Resolution	800 x 480	Size	7 "
Touch-Screen	MultiTouch, capacitive		

General data

Blickwinkel (Horizontal)	Links: 70° / Rechts: 70°	Blickwinkel (Vertikal)	Oben: 70° / Unten: 60°
Protection degree	IP66, IP4x (rear side)	Voltage supply	24 V DC

Classifications

ETIM 6.0	EC001412	eClass 6.2	27-24-23-90
eClass 9.0	27-33-02-01	eClass 9.1	27-33-02-01

Approvals

Approvals



ROHS Conform

Downloads

 User Documentation [QGUI UC20 HMI](#)