



9W

VT-2099 9W A60 THERMAL PLASTIC BULBS COLORCODE:2700K E27

Equivalent
60W

Lumens
806

Beam Angle
200

Dimensions
60x112mm

Warm White
SKU:7260



2 YEARS
WARRANTY



Technical Information

Instant Start: 0-100% in 11s

EQ-WATTS: 60

Watts: 9

Lumens: 806

Holder Type: E27

Shape: A60

Beam Angle: 200

Unit Color: White

Body Type: Thermoplastic

Energy Rating: A+

Long life: 20,000 Hours

LED Chip Type: SMD

IP Rating: IP20

Dimmable: No

Warranty (Years): 2

PF: >0.5

CRI: >80

Operation Temperature: -25 to +50°C

Input Power: AC:220-240V,50Hz



Features

- ✓ Stable SMD technology which makes the product more reliable and durable
- ✓ Uses 80% less energy and lasts 20 times longer than Standard Bulbs
- ✓ LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- ✓ High endurance and Durability
- ✓ Excellent Heat Radiation Efficiency
- ✓ Aluminium & Thermoplastic Body options available
- ✓ High luminous efficacy & Low Power consumption
- ✓ Excellent Power factor & Integrated IC driver
- ✓ No Flickering - No UV Radiation - No Mercury
- ✓ Broad Range of holders like E27, E14, B22, B15 .
- ✓ Application - Residential Lighting, Commercial Lighting, Decorative, Living Room, Lounge etc

Note:



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.066
Length(Box)mm	60
Width(Box)mm	60
Height(Box)mm	115
Unit CBM	0.000523

Master Box Packaging

Inner Box Qty	100
Master Box Qty (Pcs Per Carton)	100
Qty Per Pallet	2500

Listing Details

EAN Code	3800157622110
Commodity Code	9405403990



READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES