


Dimensions



Model Number

V1S-T-V1

Y distributor, M12 connector on M12 socket/socket

Features

- Simple assembling of 2 signals to one M12 plug-in station
- Suitable for normally open contacts or 1 signal from antivalent sensors
- Immunity to vibration
- Gold plated contacts

Technical data General specifications

Number of pins	4
Codina	Α

Electrical specifications

Operating voltage	UB	60 V
Operating current	I_B	4 A
Contact resistance		< 10 mO

Ambient conditions

Ambient temperature	-25 90 °C (-13 194 °F)
Pollution Degree	3

Mechanical specifications

Degree of protection	IP65/IP67
----------------------	-----------

Connection	1 x M12 connector, straight
	2 v M12 straight sockets

Material

Contacts	CuZn
Contact surface	Ni/Au
Body	TPU

Slotted nut Zinc die-casting, nickel-plated

Flammability

94 V-2 Housing

Compliance with standards and directives

Standard conformity

Degree of protection EN 60529

Electrical connection

