



## DVI-D Male to HDMI 1.4 Female Adapter 1080P FHD Black

### V7E2DVIDMHDMIF-ADPTR

SKU: YE3711

Why V7 Cables? + Selection - Choose from a wide variety of length and colour options. + Pricing - V7 cables are competitively priced and affordable. + Dependability - V7 cables are factory terminated and tested to ensure the highest levels of performance and reliability. + Guarantee - V7 lifetime warranty against material or manufacturing defects keeps you worry-free.

- Delivers a vivid, colorful picture
- Simple plug-and-play connectivity
- High grade shielding resistant to EMI and RF
- Built with corrosion-resistant connectors and strain relief for optimal signal transfer, fit and durability
- Manufactured in our ISO certified facilities and backed by V7's warranty

#### General

Sku: YE3711  
 Model: V7E2DVIDMHDMIF-ADPTR  
 EAN: 4038489023087  
 Warranty: Lifetime  
 Compliance: CE, RoHS, WEEE  
 Country Of Origin: Vietnam  
 Package Type: Polybag

#### Color

Color: Black

#### Package Dimensions

Package Dimensions (L/W/H): 6.3 x 8.27 x 0 in (160 x 210 x 0.1 mm)  
 Shipping Weight: 0.039 kg (0.09 lbs)

#### Product Dimensions

Product Weight: 0.03 kg (0.07 lbs)

#### Technical

Maximum Resolution: 1920 x 1080  
 Cable Length: 0.1m/0.3ft  
 Standard: DVI-D, HDMI 1.4  
 Connectors: DVI, HDMI  
 Frequency: 60 Hz  
 Fire Rating: VW-1  
 Peak Current: 0  
 Connector 1: DVI-D Male  
 Connector 2: HDMI Female  
 Data Transfer Rate: 0