



VGA Cable 1080P FHD 3m/10ft Black

V7E2VGA-03M-BLK

SKU: J151336

V7 VGA cables are designed and manufactured to meet and exceed all category specifications to ensure reliable performance when connecting PCs, monitors, HDTVs and video projectors. VGA Monitor and Extension Cables ensure high-quality displays for VGA-connected devices.

- Delivers a vivid, colorful picture
- Simple plug-and-play connectivity
- High grade shielding resistant to EMI and RF
- Built with corrosion-resistant connectors and strain relief for optimal signal transfer, fit and durability
- Manufactured in our ISO certified facilities and backed by V7's warranty

General

Sku: J151336
 Model: V7E2VGA-03M-BLK
 UPC: 662919033427
 Warranty: 2 years
 Compliance: CE, RoHS, WEEE
 Country Of Origin: Vietnam
 Package Type: Polybag

Color

Color: Black

Package Dimensions

Package Dimensions (L/W/H): 7.48 x 9.45 x 0 in (190 x 240 x 0.1 mm)
 Shipping Weight: 0.24 kg (0.53 lbs)

Product Dimensions

Product Weight: 0.23 kg (0.51 lbs)

Technical

Maximum Resolution: 1920 x 1080
 Conductor: Tin Plated Copper
 Cable Length: 3m/10ft
 Conductor Size: 28AWG/30AWG
 Shielding: Aluminum Mylar foil with Braid
 Connectors: VGA
 Frequency: 60 Hz
 Fire Rating: VW-1
 Cable diameter: 6.2mm
 Connector 1: VGA Male
 Connector 2: VGA Male
 Number of Conductors: 13