



V7 Bluetooth Wireless Stereo Headset

HB600S

SKU: 7FL290

Today's open workspaces can be full of distractions, so you need a headset that's ready for business. V7's HB600S Bluetooth® Wireless Headset was designed to allow focus and improve productivity in business environments. Connect to your PC or smartphone to experience amazing clarity with popular conferencing programs like Microsoft Teams, Zoom, Google Voice, Skype and others, or while listening to your favorite music. Built for all-day comfort, with on-headset controls and an impressive 30-meter (100') range, V7's wireless headsets are perfect choice to enhance your workplace efficiency.

- Bluetooth v5.0
- Up to 18 Hours Talk-time; 175 Hours Standby
- Detachable Boom Microphone
- Includes V7 Link Audio Bluetooth v5.0 USB Dongle
- USB-C Connector for Charging
- Designed for Windows 10, macOS, iOS and Android devices
- Optional Charging Cradle Available

General

Sku: 7FL290
 Model: HB600S
 EAN: 0662919107715
 Warranty: 2 years
 Compliance: BQB, CE, FCC, RoHS
 Country Of Origin: China
 Package Type: 4 Color Box
 Package Includes: Headset, Detachable Boom Mic, USB Dongle, USB Charging Cable, 3.5mm AUX Cable, Storage Bag, User's Guide, Warranty and Compliance documents

Color

Color: Black
 Accent Color: Gray

Design

Audio Segment: Bluetooth Wireless
 Headset Form Factor: On Ear
 Controls: Power, Pairing, Volume, Track Forward, Repeat, Pause, Mute, Call Answer, End

Package Dimensions

Package Dimensions (L/W/H): 206 x 186 x 55mm
 (8.11 x 7.32 x 2.17")
 Package Weight: 368.5g (13 oz)

Product Dimensions

Product Dim (L/W/H): 158.8 x 186.7 x 71.1mm (6.25 x 7.35 x 2.8")
 Product Weight: 158.3g (5.56 oz)

California Prop 65

No warning required

Technical

Connectivity: Bluetooth
 Decibels: 101 dB ±3
 Impedance: 32 ohms
 Driver Size: 30mm
 Mic Sensitivity: -42 db ±3



Specifications

Battery type: Lithium Polymer (350mAh)

Speaker sensitivity: 99dB±3dB

Speaker max input power: 80mW

Speaker frequency range: 20Hz-20000Hz

Speaker bandwidth-Music mode: 20Hz-20000Hz

Speaker bandwidth-Speak mode: 100Hz-10000Hz

Microphone type: Omnidirectional Microphone

Microphone frequency range: 100Hz-10000Hz

Audio Codecs supported: SBC

Music time: Up to 18 hours

Talk time: Up to 18 hours

Charging time: About 3 hours

Power consumption: 310mA

Connection: Bluetooth, Bluetooth Dongle, 3.5 Analog AUX

Bluetooth version: V5.0

Bluetooth profiles: A2DPv1.3.1, AVRCPv1.6, HFPv1.7, HSPv1.2, SPP v1.2, DID v1.3, HID v1.1, PXP v1.0.1, FMP v1.0, BAS v1.0

Operating range: Up to 30m line of site

Bluetooth pairing list: 8

Simultaneous Bluetooth connections: 2