





V7 Bluetooth® Wireless Mono Headset

HB605M

SKU: 7FL291

Enjoy superior wireless connectivity with V7's HB605M Bluetooth® Wireless Mono Headset. With a range of up to 30 meters or 100 feet, you can walk away from your desk without the hassle for dropped connections. Wirelessly connect the HB605M via Bluetooth (Includes a USB dongle for PC connectivity) to your PC or smartphone to experience amazing clarity for conference calls with Microsoft Teams, Zoom, Google Meet and other popular conferencing programs. Our mono headset is lightweight, built for all-day comfort, includes on-headset controls and an impressive 30-meter (100') range, V7's wireless headsets are perfect choice to enhance your workplace efficiency.

- Bluetooth v5.0
- Up to 18 Hours Talk-time; 175 Hours Standby
- Detachable Boom Microphone
- Includes V7 Link Audio Bluetooth v5.0 USB Dongle
- USB-C Connector for Charging
- Designed for Windows 10, macOS, iOS and Android devices
- Optional Charging Cradle Available

General

Sku: 7FL291
Model: HB605M
EAN: 0662919107722
Warranty: 2 years
Compliance: BQB, CE, FCC, RoHS
Country Of Origin: China
Package Type: 4 Color Box
Package Includes: Headset, Detachable Boom Mic, USB Dongle, USB Charging Cable, 3.5mm AUX Cable, Storage Bag, User's Guide, Warranty and Compliance document

Color

Color: Black
Accent Color: Gray

Design

Audio Segment: Bluetooth Wireless
Headset Form Factor: On Ear
Controls: Power, Pairing, Volume, Mute, Call Answer, End

Package Dimensions

Package Dimensions (L/W/H): 206 x 186 x 55mm (8.11 x 7.32 x 2.17")
Package Weight: 296.7g (10.5 oz)

Product Dimensions

Product Dim (L/W/H): 158.8 x 186.7 x 71.1mm (6.25 x 7.35 x 2.8")
Product Weight: 144.3g (5.09 oz)

California Prop 65

No warning required

Technical

Connectivity: Bluetooth
Decibels: 101 dB ±3
Impedance: 32 ohms
Driver Size: 30mm
Mic Sensitivity: -42 db ±3

The data in this publication is for illustration purposes only and does not necessarily represent standards or specifications which must be met by V7. Design and specifications are subject to change without prior notice. Trademarks belong to their respective owners. No responsibility assumed and all liability for damages resulting from use of this information or for any errors or omissions, are disclaimed. Measurement standards and testing conditions, as per manufacturer definitions, are available on request. Last Updated: August 25, 2021 09:48

Specifications

Battery type: Lithium Polymer (350mAh)
Speaker sensitivity: 99dB±3dB
Speaker max input power: 80mW
Speaker frequency range: 20Hz-20000Hz
Speaker bandwidth-Music mode: 20Hz-20000Hz
Speaker bandwidth-Speak mode:100Hz-10000Hz
Microphone type: Omnidirectional Microphone
Microphone frequency range: 100Hz-10000Hz
Audio Codecs supported: SBC
Music time: Up to 18 hours
Talk time: Up to 18 hours

Charging time: About 3 hours
Power consumption: 310mA
Connection: Bluetooth, Bluetooth Dongle, 3.5 Analog AUX
Bluetooth version: V5.0
Bluetooth profiles: A2DPv1.3.1, AVRCPv1.6, HFPv1.7, HSPv1.2, SPP v1.2, DID v1.3, HID v1.1, PXP v1.0.1, FMP v1.0, BAS v1.0
Operating range: Up to 30m line of site
Bluetooth pairing list: 8
Simultaneous Bluetooth connections: 2

The data in this publication is for illustration purposes only and does not necessarily represent standards or specifications which must be met by V7. Design and specifications are subject to change without prior notice. Trademarks belong to their respective owners. No responsibility assumed and all liability for damages resulting from use of this information or for any errors or omissions, are disclaimed. Measurement standards and testing conditions, as per manufacturer definitions, are available on request. Last Updated: August 25, 2021 09:48