



## V7 23.8" FHD 1920x1080 Height Adjustable IPS LED Monitor

### L238IPS-HAS-E

SKU: CD36508

The sleek and stylish 23.8" monitor from V7 is a stunning display and features a height adjustable stand with swivel and tilt for optimum ergonomics. It boasts a HDMI, VGA and DisplayPort inputs, so you can be sure it will work with virtually any machine you want to connect. With full HD 1920x1080 resolution, vivid colors and integrated speakers, this display provides a rich, multi-media experience for business or pleasure. Additionally, the display is VESA 100x100mm mountable to optimize your workspace, plus it's backed by a 3 year manufacturer's warranty.

- Height-adjustable stand with swivel, tilt, and pivot, to optimize position and viewing angle
- Ultra-thin bezel design for a high-end appearance
- Input options HDMI, DisplayPort and VGA – HDMI cable included
- Mount ready with 100 x 100 VESA pattern
- 1920 x 1080 Full HD Resolution for an excellent viewing experience

#### General

Sku: CD36508  
 Model: L238IPS-HAS-E  
 EAN: 0662919114904  
 Warranty: 3 years  
 Compliance: CE, Energy Star, FCC, RoHS, UKCA, WEEE  
 Country Of Origin: China  
 Package Type: One Color  
 ASIN: B09M8STB12  
 SAP: 5349841  
 Package Includes: Monitor with Height Adjustable Stand, VESA Adapter, 2 x M4x12, 2 x M4x30, Quick installation guide, HDMI Cable, EU and UK Power Cord, Power Adapter, Warranty Card

#### Color

Color: Black

#### Design

Monitor Feature: Height Adjustable

#### Package Dimensions

Package Dimensions (L/W/H): 59.4 x 14.5 x 40.1 cm (23.4 x 5.7 x 15.8 in)  
 Shipping Weight: 4.8 kg (10.6 lbs)  
 Package Weight: 4.8 kg (10.6 lbs)

#### Product Dimensions

Product Dim (L/W/H): 54.2 x 21 x 48.6 cm (21.3 x 8.3 x 19 in)  
 Product Weight: 3.82 kg (8.4 lbs) / without stand  
 2.37 kg (5.22 lbs)

#### Technical

MTBF: 30,000 hrs  
 Panel Size: 23.8 in  
 Panel Type: IPS  
 Power Input: AC 100V-240V 50-60Hz  
 Aspect Ratio: 16:9  
 Response Time: 14 ms  
 Viewing Angle: 178°H / 178°V  
 Maximum Resolution: 1920 x 1080  
 Screen Coating: Matte  
 Brightness: 220 nits  
 Color Depth: 16.7 million colors  
 EU/UK Energy Rating: F  
 Contrast Ratio: 1200:1  
 Input Port: DisplayPort, HDMI, VGA  
 VESA Mount: 100 x 100 mm  
 Input AC Plug Type: BS 1363 (UK) and Schuko (EU)  
 Stand: 34.9 cm (13.7 in) H, 20.5 cm (8 in) D  
 Speaker: 2 x 2W  
 Monitor Dim (w/o Stand): 54.2 x 32.1 x 5.4cm (21.3 x 12.6 x 2.1in)  
 Pixel Pitch (H/V): 0.2745 (H) x 0.2745 (V)  
 Horizontal Frequency: 60Hz  
 Display Area (H x L): 52.7 cm x 29.6 cm