



USB A Female to USB A Male USB 2.0 Extension Cable 480 Mbps 1.8m/6ft Black

V7E2USB2EXT-1.8M

SKU: J151411

Why V7 Cables? Selection - Choose from a wide variety of length and colour options. Pricing - V7 cables are competitively priced and affordable. Dependability - V7 cables are factory terminated and tested to ensure the highest levels of performance and reliability. Guarantee - V7 lifetime warranty against material or manufacturing defects keeps you worry-free.

- Faster charging and data communication between devices
- Simple plug-and-play connectivity
- High grade shielding resistant to EMI and RF
- Built with corrosion-resistant connectors and strain relief for optimal signal transfer, fit and durability
- Manufactured in our ISO certified facilities and backed by V7's warranty

General

Sku: J151411
 Model: V7E2USB2EXT-1.8M
 UPC: 662919033342
 Warranty: Lifetime
 Compliance: CE, RoHS, WEEE
 Country Of Origin: Vietnam
 Package Type: Polybag

Color

Color: Black

Package Dimensions

Package Dimensions (L/W/H): 6.3 x 8.27 x 0 in (160 x 210 x 0.1 mm)
 Shipping Weight: 0.07 kg (0.15 lbs)

Product Dimensions

Product Weight: 0.06 kg (0.13 lbs)

Technical

Conductor: Tin Plated Copper
 Cable Length: 1.8m/6ft
 Conductor Size: 28AWG
 Shielding: Aluminum Mylar foil with Braid
 Standard: USB 2.0
 Connectors: USB
 Fire Rating: VW-1
 Cable diameter: 4.0mm
 Connector 1: USB A Female
 Connector 2: USB A Male
 Number of Conductors: 4
 Data Transfer Rate: 480 Mbps