



USB A Female to USB A Male USB 3.2 Gen 1 Extension Cable 5 Gbps 3m/10ft Black

V7E2USB3EXT-03M

SKU: J151674

Why V7 Cables? + Selection - Choose from a wide variety of length and colour options. + Pricing - V7 cables are competitively priced and affordable. + Dependability - V7 cables are factory terminated and tested to ensure the highest levels of performance and reliability. + Guarantee - V7 lifetime warranty against material or manufacturing defects keeps you worry-free.

- Faster charging and data communication between devices
- Simple plug-and-play connectivity
- High grade shielding resistant to EMI and RF
- Built with corrosion-resistant connectors and strain relief for optimal signal transfer, fit and durability
- Manufactured in our ISO certified facilities and backed by V7's warranty

General

Sku: J151674
 Model: V7E2USB3EXT-03M
 EAN: 4038489023148
 Warranty: Lifetime
 Compliance: CE, RoHS, WEEE
 Country Of Origin: Vietnam
 Package Type: Polybag

Color

Color: Black

Package Dimensions

Package Dimensions (L/W/H): 7.48 x 9.45 x 0 in (190 x 240 x 0.1 mm)
 Shipping Weight: 0.127 kg (0.28 lbs)

Product Dimensions

Product Weight: 0.12 kg (0.26 lbs)

Technical

Conductor: Tin Plated Copper
 Cable Length: 3m/10ft
 Conductor Size: 28AWG
 Shielding: Aluminum Mylar foil with Braid
 Standard: USB 3.2 Gen 1
 Connectors: USB
 Fire Rating: VW-1
 Cable diameter: 5.5mm
 Connector 1: USB A Female
 Connector 2: USB A Male
 Number of Conductors: 9
 Data Transfer Rate: 5 Gbps