



## USB A Female to USB A Male USB 3.2 Gen1 Extension Cable 5 Gbps 2m/6.6ft Black

### V7U3.0EXT-2M-BLK-1E

SKU: J153346

Why V7 Cables? Selection - Choose from a wide variety of length and colour options. Pricing - V7 cables are competitively priced and affordable. Dependability - V7 cables are factory terminated and tested to ensure the highest levels of performance and reliability. Guarantee - V7 lifetime warranty against material or manufacturing defects keeps you worry-free.

- Faster charging and data communication between devices
- Simple plug-and-play connectivity
- High grade shielding resistant to EMI and RF
- Built with corrosion-resistant connectors and strain relief for optimal signal transfer, fit and durability
- Manufactured in our ISO certified facilities and backed by V7's warranty

#### General

Sku: J153346  
 Model: V7U3.0EXT-2M-BLK-1E  
 UPC: 662919088793  
 Warranty: Lifetime  
 Compliance: CE, RoHS, WEEE  
 Country Of Origin: Vietnam  
 Package Type: Polybag  
 SAP: 3292784

#### Color

Color: Black

#### Package Dimensions

Package Dimensions (L/W/H): 6.3 x 8.27 x 0 in (160 x 210 x 0.1 mm)  
 Shipping Weight: 0.105 kg (0.23 lbs)

#### Product Dimensions

Product Weight: 0.1 kg (0.22 lbs)

#### Technical

Conductor: Tin Plated Copper  
 Cable Length: 2m/6.6ft  
 Conductor Size: 28AWG  
 Shielding: Aluminum Mylar foil with Braid  
 Standard: USB 3.2 Gen 1  
 Connectors: USB  
 Fire Rating: VW-1  
 Cable diameter: 5.5mm  
 Connector 1: USB A Female  
 Connector 2: USB A Male  
 Number of Conductors: 9  
 Data Transfer Rate: 5 Gbps