


# blinking plate VABB-L1-18

Part number: 574482

★ Core product range

FESTO



## Data sheet

Feature	Value
Grid dimension	19 mm
Operating pressure MPa	-0.09 ... 1 MPa
Operating pressure	-0.9 ... 10 bar
Authorisation	RCM Mark c CSA us (OL) c UL us - Recognized (OL)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Max. tightening torque, valve mounting	1.18 Nm
Product weight	50 g
Materials note	Conforms to RoHS
Material cover plate	Wrought Aluminium alloy