



VET M12 SV EPDM

E1458181

VET-GROMMETS, EPDM BLACK, M12, 3-5mm

Single gate seals with strain relief.

Pull the cable through and then pull back for locking.

Fits in sheet metal with wall thickness 1.0-4.0 mm(PG) or 1.3-5.0 mm(Metric)

Product Properties:

Gastight	No
Degree of protection (IP)	IP67
Watertight	Yes, No
Fire resistant	No
Angle model	No
With strain relief	No
Model	Closed
Material quality	Ethylene-propylene diene monomer rubber (EPDM)
Shrink technique	No
Insert for cable gland	No
Cable entry	Round
Colour	Black
Surface protection	Untreated
Material	Rubber
Halogen free	Yes
Number of cables	1 .
Operating temperature	-40-100 °C

Dimensions:

Unit	pcs
-------------	-----

OD	19 mm
CD	3-5 mm
BD	12.2 mm
WT	1.3-5 mm
L	18.5 mm
Bore diameter	12.2 mm
For wall thickness	1.3-5 mm
Suitable for cable diameter	3-5 mm
Thread size (metric)	12 .
MOQ	50 .

Approvals:

Degree of protection (IP)	IP67
---------------------------	------

Compliance:

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (Latest)
SCIP	Not Applicable

Other information:

ETIM-Class	EC000879 - Cable entry sleeve
ETIM-Release	7.0
Product Group	VET-grommets
Search Description	VET-HYLSA, EPDM
Alternative SKU	VETM12SVEPDM

Logistic information:

Barcode	733117610223
E-no	E1458181
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	VET M12 SV EPDM
Taric code	40169300
Unit	pcs
MOQ	50 .