



## VET M25 SV EPDM

E1458184

VET-GROMMETS, EPDM BLACK, M25, 10-14mm

Single gate seals with strain relief.

Pull the cable through and then pull back for locking.

Fits in sheet metal with wall thickness 1.0-4.0 mm(PG) or 1.3-5.0 mm(Metric)

## Product Properties:

<b>Gastight</b>	No
<b>Degree of protection (IP)</b>	IP67
<b>Watertight</b>	Yes, No
<b>Fire resistant</b>	No
<b>Angle model</b>	No
<b>With strain relief</b>	No
<b>Model</b>	Closed
<b>Material quality</b>	Ethylene-propylene diene monomer rubber (EPDM)
<b>Shrink technique</b>	No
<b>Insert for cable gland</b>	No
<b>Cable entry</b>	Round
<b>Colour</b>	Black
<b>Surface protection</b>	Untreated
<b>Material</b>	Rubber
<b>Halogen free</b>	Yes
<b>Number of cables</b>	1 .
<b>Operating temperature</b>	-40-100 °C

## Dimensions:

<b>Unit</b>	pcs
-------------	-----

OD	32 mm
CD	10-14 mm
BD	25.2 mm
WT	1.3-5 mm
L	19.5 mm
Bore diameter	25.2 mm
For wall thickness	1.3-5 mm
Suitable for cable diameter	10-14 mm
Thread size (metric)	25 .
MOQ	50 .

### **Approvals:**

Degree of protection (IP)	IP67
---------------------------	------

### **Compliance:**

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (Latest)
SCIP	Not Applicable

### **Other information:**

ETIM-Class	EC000879 - Cable entry sleeve
ETIM-Release	7.0
Product Group	VET-grommets
Search Description	VET-HYLSA, EPDM
Alternative SKU	VETM25SVEPDM

### **Logistic information:**

Barcode	733117610271
E-no	E1458184
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	VET M25 SV EPDM
Taric code	40169300
Unit	pcs
MOQ	50 .