



VET M40 GR EPDM

E1458176

VET-GROMMETS, EPDM GREY RAL 7042, M40, 20-26mm

Single gate seals with strain relief.

Pull the cable through and then pull back for locking.

Fits in sheet metal with wall thickness 1.0-4.0 mm(PG) or 1.3-5.0 mm(Metric)

Product Properties:

Gastight	No
Degree of protection (IP)	IP67
Watertight	Yes, No
Fire resistant	No
Angle model	No
With strain relief	No
Model	Closed
For slotted hole	No
Material quality	Ethylene-propylene diene monomer rubber (EPDM)
Shrink technique	No
Insert for cable gland	No
Cable entry	Round
Colour	Grey
Surface protection	Untreated
Material	Rubber
Halogen free	Yes
Number of cables	1 .
Operating temperature	-40-100 °C

Dimensions:

Unit	pcs
OD	47 mm
CD	20-26 mm
BD	40.2 mm
WT	1.3-5 mm
L	24 mm
Bore diameter	40.2 mm
For wall thickness	1.3-5 mm
Suitable for cable diameter	20-26 mm
Thread size (metric)	40 .
MOQ	10 .

Approvals:

Degree of protection (IP)	IP67
---------------------------	------

Compliance:

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (Latest)
SCIP	Not Applicable

Other information:

Trademark	NEMIQ
ETIM-Class	EC000879 - Cable entry sleeve
ETIM-Release	7.0
Product Group	VET-grommets
Alternative SKU	VETM40GREPDM

Logistic information:

Barcode	733117638994
E-no	E1458176
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	VET M40 GR EPDM
Taric code	40169300
Unit	pcs
MOQ	10 .