



VET M40 SV EPDM

E1458186

VET-GROMMETS, EPDM BLACK, M40, 20-26mm

Single gate seals with strain relief.

Pull the cable through and then pull back for locking.

Fits in sheet metal with wall thickness 1.0-4.0 mm(PG) or 1.3-5.0 mm(Metric)

Product Properties:

Gastight	No
Degree of protection (IP)	IP67
Watertight	Yes, No
Fire resistant	No
Angle model	No
With strain relief	No
Model	Closed
Material quality	Ethylene-propylene diene monomer rubber (EPDM)
Shrink technique	No
Insert for cable gland	No
Cable entry	Round
Colour	Black
Surface protection	Untreated
Material	Rubber
Halogen free	Yes
Number of cables	1 .
Operating temperature	-40-100 °C

Dimensions:

Unit	pcs
-------------	-----

OD	47 mm
CD	20-26 mm
BD	40.2 mm
WT	1.3-5 mm
L	24 mm
Bore diameter	40.2 mm
For wall thickness	1.3-5 mm
Suitable for cable diameter	20-26 mm
Thread size (metric)	40 .
MOQ	10 .

Approvals:

Degree of protection (IP)	IP67
---------------------------	------

Compliance:

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (Latest)
SCIP	Not Applicable

Other information:

ETIM-Class	EC000879 - Cable entry sleeve
ETIM-Release	7.0
Product Group	VET-grommets
Search Description	VET-HYLSA, EPDM
Alternative SKU	VETM40SVEPDM

Logistic information:

Barcode	733117610267
E-no	E1458186
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales., Non Stock Item, can be on stock but is not a regular stock item.
Stock code	VET M40 SV EPDM
Taric code	40169300
Unit	pcs
MOQ	10 .