



**VET M60 GR EPDM**

E1458178

VET-GROMMETS, EPDM GREY RAL 7042, M60, 30-45mm

Single gate seals with strain relief.

Pull the cable through and then pull back for locking.

Fits in sheet metal with wall thickness 1.0-4.0 mm(PG) or 1.3-5.0 mm(Metric)

**Product Properties:**

<b>Gastight</b>	No
<b>Degree of protection (IP)</b>	IP67
<b>Watertight</b>	Yes, No
<b>Fire resistant</b>	No
<b>Angle model</b>	No
<b>With strain relief</b>	No
<b>Model</b>	Closed
<b>For slotted hole</b>	No
<b>Material quality</b>	Ethylene-propylene diene monomer rubber (EPDM)
<b>Shrink technique</b>	No
<b>Insert for cable gland</b>	No
<b>Cable entry</b>	Round
<b>Colour</b>	Grey
<b>Surface protection</b>	Untreated
<b>Material</b>	Rubber
<b>Halogen free</b>	Yes
<b>Number of cables</b>	1 .
<b>Operating temperature</b>	-40-100 °C

## **Dimensions:**

Unit	pcs
OD	69 mm
CD	30-45 mm
BD	60.2 mm
WT	1.3-5 mm
L	45 mm
Bore diameter	60.2 mm
For wall thickness	1.3-5 mm
Suitable for cable diameter	30-45 mm
Thread size (metric)	60 .
MOQ	10 .

## **Approvals:**

Degree of protection (IP)	IP67
---------------------------	------

## **Compliance:**

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (Latest)
SCIP	Not Applicable

## **Other information:**

Trademark	NEMIQ
ETIM-Class	EC000879 - Cable entry sleeve
ETIM-Release	7.0
Product Group	VET-grommets
Alternative SKU	VETM60GREPDM

## **Logistic information:**

Barcode	733117638996
E-no	E1458178
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	VET M60 GR EPDM
Taric code	40169300
Unit	pcs
MOQ	10 .