

VALUE Cat.6A (Class EA) 19" Patch Panel, 24 Ports, UTP, black

Product No.	26.99.0357
Manufacturer	VALUE
Manufacturer No.	26.99.0357
EAN (single piece)	7630049611108



24-port CAT. 6A patch panel for use in 19" network environments with up to 10 Gigabit Ethernet.

- The VALUE Cat. 6A 19" patch panels fulfil the Cat. 6A/Class EA permanent link standard and are ideal for 10 Gigabit Ethernet networks
- Cable assembly takes place using LSA plus piercing terminals with colour coding on the top in accordance with EIA/TIA 568A
- Sheet steel
- Colour: black

Technical specifications

Manufacturer	VALUE
Product group	Connection technology TP
Product type	Patchpanel Cat.6A / Class EA
Colour	black
Shield type	Not screened
Transfer quality	Cat6A / Class EA
Cabinet system	19"-Technique
Quantity of ports	24
Assembly cable connection	Krone LSAplus

Assignment	EIA/TIA 568A & 568B
Modular assembly	No
Material (casing)	Metal
separate strain relief	Yes
Height units	1 UH
Height	44.5 mm
Width	482.5 mm
Depth	100 mm
Weight	706.5 g
Height of packaging (single piece)	60 mm
Width of packaging (single piece)	100 mm
Depth of packaging (single piece)	520 mm
Package weight (single piece)	0.9 kg