

# VALUELINE

## DVI Cable DVI-D 24+1-Pin Male - DVI-D 24+1-Pin Male 2.00 m Black

### General information

With this DVI-D cable you can transmit digital signals between for example a computer and a LCD monitor.

### Specifications

Connector design - side B:	Straight
Diameter:	7.5 mm
AWG value:	30
Plating:	Nickel
Max. resolution:	2560x1600
Length:	2.00 m
Cable design:	Round
Connector design - side A:	Straight
Outside material:	PVC
Packaging:	Polybag
Conductor material:	Copper
Colour:	Black
Connection B:	DVI-D 24+1-Pin Male
Cable type:	DVI
Connection A:	DVI-D 24+1-Pin Male

### Package contents

- 1x DVI cable



### Sales information

Order code:	<b>VLCP32000B20</b>
Product description:	DVI Cable DVI-D 24+1-Pin Male - DVI-D 24+1-Pin Male 2.00 m Black
Packaging:	Polybag
Brand name:	Valueline



Quantity	LxWxH (mm)	Weight
1	145x30x130	218 gr.
40	315x310x400	9700 gr.
50	340x285x400	10080 gr.